

PRODUCT INFORMATION SHEET

CARLUBE COPPER GREASE

DESCRIPTION

Copper Grease is a high performance lead-free anti-seize compound which is designed for application to threads of nuts and bolts prior to assembly to ensure easy release, without damage, even after long periods in adverse conditions. The product is based on a non-melting grease containing a complex blend of heat resistant solids and low shear metals.

ADVANTAGES

- Helps initial assembly making tightening easier and more positive
- Prevents galling and seizure even at extreme temperatures and used in atmospheric conditions that would destroy other lubricants
- Excellent corrosion resistance
- Eases dismantling where metal pickup can occur

APPLICATIONS

Battery terminals, Disc pad brakes, Exhaust clamps, Spark plug threads, Wheel studs etc.

WARNING: Copper grease helps prevent disc brake squeal if applied to back of disc pads, do not apply any compound to friction material or disc electrical system.

PROPERTIES

Color	Copper
Texture	Smooth
Drop Point	Non-melting
Temperature Range (°C)	-30 – 1100
Density @ 15°C	1.200
Oil Viscosity @ 40°C (cSt)	98.8
Types of anti-seize solids	Copper, Graphite
Storage Life	5 years


AVAILABILITY

20gram – XCG020

70gram – XCG070

500gram – XCG500

3kg – YGC003

**DISCLAIMER**

This Product Information Sheet does not constitute to any extent a fitness for purpose warranty or a quality specification. It is intended to be indicative only of the general characteristics of the product(s) and may not be relied upon (in whole or in part) in substitution of nor as a supplement to any of the information and/or instructions and/or warnings set out on the product(s) and/or on any packaging and/or in the relevant Safety Data Sheet (which is available on request).

Neither of the publisher of this Product Information Sheet or the product(s) manufacturer accepts liability for the failure of any person to observe and follow the information and/or instructions and/or warnings on the product(s) and/or on any packaging and/or in the relevant Safety Data Sheet.

Any person selecting and using or causing the product(s) to be used for a specific purpose or any third party recommending the product(s) for a specific purpose without in either case first making all appropriate inquiries as to the suitability of the product(s) for the intended purpose does so at his/her/their own risk and no liability is accepted by the publisher or the product(s) manufacturer for any consequent loss, damage or injury, other than such liability as may not (by operation of law) be excluded.

This Product Information Sheet does not apply to the use of the product(s) in any combination or with other products or materials.

Users of a product or products marked "For Professional Use Only are deemed to declare and acknowledge for themselves professional levels of skill, knowledge, competence and experience in the selection and use of such product(s).

Product Information Sheets are updated from time to time and inquiries should be made on a regular basis to ensure that this is the latest version available.

TETROSYL LIMITED
BEVIS GREEN WORKS
WALMERSLEY
BURY
BL9 6RE
0161 764 5981
0161 797 5899
info@tetrosyl.com