#### Series Kraftform Micro







**EAN/GTIN:** 4013288032003 **Dimension:** 157x13x13 mm

 Part no.:
 05118092001
 Weight:
 14 g

 Article no.:
 2052 Micro
 Country of origin:
 CZ

Customs tariff 82054000

number:















- · Kraftform Micro screwdriver with ballpoint for hexagon socket screws
- Multi-component Kraftform Micro handle with anti-roll feature and swivel cap
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Ballpoint for dependable working even in difficult installation situations
- E.g. for electricians, opticians, precision mechanics, jewellers or IT hardware fitters

High quality Wera Micro screwdriver for precision mechanical work. Ballpoint profile: the ballpoint drive profile means that it is possible to swivel the tool axis away from the screwdriving axis, thus enabling "round the corner" screwdriving. Rapid twisting is possible by fixing the hand on the twist cap and using the fast-turning zone just below it. This makes time-consuming grip adjustments unnecessary. Power zone with integrated soft zones ensure the transfer of higher tightening and loosening torque. Precision zone for the right angle for adjustment work. The Wera Black Point tip offers high corrosion protection and an exact fit.

#### Series Kraftform Micro



#### Ball tip



Kraftform Micro Handle





Screwdriving jobs in electrical and precision engineering applications are often tedious and timeconsuming. We learned from users what is important for them: working speeds, torque, precision - and we then focused particularly on these issues.



The spherical drive profile means that it is possible to swivel the axis of the tool to that of the screw, and therefore enable angled, "around-the-corner" screwdriving jobs.

Multi-component screwdriver handle for ergonomic working.



The precision zone

The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

#### The power zone



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

### The fast-turning zone



The fast-turning zone just below the rotating cap allows rapid twisting.

#### The refined screwdriver for electronics technicians



The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The freeturning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

### Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.

# 2052 Ball end hexagon screwdriver for electronic applications, 2.0 mm x 60 mm

## Series Kraftform Micro



## More variants of this product family:

	0	0	A	↓ Å	$\varnothing$	<b>∏</b>
	mm	inch	mm	mm	mm	inch
05118089001	1.3	-	60	97	3.0	2 3/8
05118090001	1.5	-	60	97	3.0	2 3/8
05118092001	2.0	-	60	97	3.0	2 3/8
05118094001	2.5	-	60	97	4.0	2 3/8
05118096001	3.0	-	60	97	4.0	2 3/8
05118098001	-	1/16	60	97	3.0	2 3/8
05118100001	-	5/64	60	97	3.0	2 3/8
05118102001	=	3/32	60	97	3.0	2 3/8
05118106001	-	7/64	60	97	4.0	2 3/8
05118103001	-	1/8	60	97	4.0	2 3/8