

MLBL-01R



Products → Low Voltage Products and Systems → Control Products → Pilot Devices → Pilot Devices Accessories

General Information

Extended Product Type:	MLBL-01R
Product ID:	1SFA611621R1011
EAN:	7320500372906
Catalog Description:	MLBL-01R LED block
Long Description:	Modular LED block - 24V AC / DC, integrated LED - Red - Illuminated

Ordering

EAN:	7320500372906
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369001

Dimensions

Product Net Width:	0.044 m
Product Net Height:	0.010 m
Product Net Depth / Length:	0.035 m
Product Net Weight:	0.01 kg

Container Information

Package Level 1 Width:	0.11 m
Package Level 1 Height:	0.01 m
Package Level 1 Depth / Length:	0.15 m
Package Level 1 Gross Weight:	0.01 kg

Additional Information

Accessory Type:	LED and lamp blocks
Color:	Red
Illumination:	Illuminated
Lamp Type:	24V AC / DC, integrated LED
Luminance:	250 millicandela
Mounting Type:	Front mounting
Product Main Type:	MLBL
Product Name:	LED block
Product Range:	Modular range
Product Type:	MLBL
Rated Current (I_n):	9.9 mA

Rated Operational Voltage:

24 V AC/DC

Suitable For:

MP1
MP2
MP3
MP4
MPD1
MPD2
MPD3
MPD4
MPD5
MPD11
MPD12
MPD13
MPD14
MPD15
MPD16
MPM1
MPM2
KP6
MPET3
MPEP3
MPEK3
MPET4
MPEP4
MPEK4
MPMT3
MPMT4
MPMP3
MPMP4
M2SS1
M2SS2
M2SS3
M2SS4
M2SS5
M2SS6
M3SS1
M3SS2
M3SS3
M3SS4
M3SS5
M3SS6
M3SS7
M3SS8
M3SSC1
M3SSC2
M3SSC3
M3SSC4
M3SSC5
M3SSC6
M3SSC7
M3SSC8

M2SSK0
M2SSK1
M2SSK2
M2SSK3
M3SSK1
M3SSK2
M3SSK3
MTS1
MTS2
MTS3
MJS1
MJS2
MJS5
MJS6
MJS7
MJS8
MJS11
MJS12

Wave Length: 620 nm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SFC151005C0201
Declaration of Conformity - CE:	1SFA1-83
Environmental Information:	1SFC151010D0201
Instructions and Manuals:	1SFC151005C0201

Classifications

E-nummer:	3705054
ETIM 4:	EC002024 - Accessories for control circuit devices
ETIM 5:	EC000204 - Lamp holder block for control circuit devices
ETIM 6:	EC000204 - Lamp holder block for control circuit devices
Object Classification Code:	E
UNSPSC:	39120000

