

**Blanking plugs
VP M32-MS65**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

| | |
|------------|---|
| Type | VP M32-MS65 |
| Order No. | 1777760000 |
| Version | Blanking plugs, Blanking plug, M 32, 8 mm, Brass, nickel-plated |
| GTIN (EAN) | 4032248158034 |
| Qty. | 50 pc(s). |

**Blanking plugs
VP M32-MS65**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Length | 12 mm | Length (inches) | 0.472 inch |
| Height | 12 mm | Height (inches) | 0.472 inch |
| Net weight | 27.08 g | Diameter | 35 mm |

General information

| | | | |
|-----------------------------------|----------------------|-----------------------------------|--------|
| Cable gland | metric | External thread | M 32 |
| Head diameter | 35 mm | Length of thread | 8 mm |
| Material | Brass, nickel-plated | O-Ring | NBR |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
| Pitch of thread | 1.5 mm | Protection degree | IP68 |
| Sealing | NBR | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000032 | ETIM 4.0 | EC000032 |
| ETIM 5.0 | EC000032 | ETIM 6.0 | EC000451 |
| UNSPSC | 30-21-18-01 | eClass 5.1 | 27-14-91-10 |
| eClass 6.2 | 27-14-91-10 | eClass 7.1 | 27-14-91-10 |
| eClass 8.1 | 27-14-91-10 | eClass 9.0 | 27-14-44-33 |
| eClass 9.1 | 27-14-44-33 | | |

Product information

Descriptive text ordering data Other versions available on request. The blanking plugs must be tightened "hand-tight" with the screwdriver.

Approvals

Approvals



ROHS Conform

Downloads

| | |
|--------------------|---|
| Brochure/Catalogue | CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN |
| Engineering Data | EPLAN_WSCAD |

Data sheet

**Blanking plugs
VP M32-MS65**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

