

4-1/2 IN. ANGLE GRINDER

- Metal gear case dissipates heat for longer life.
- 2 position side handle for right or left hand use.
- Spindle lock for quick wheel/blade changes.
- 5/8"-11 spindle for mounting the most popular 4 to 4-1/2" wheels.
- cETL listed 315240

Bonus pack includes: 4-1/2" grinding wheel, 2 - type 1 metal cut off wheels, 40, 80 and 120 grit flap discs, side handle. Also comes with replaceable motor brushes to extend tool life and spindle wrench.



| Item # | IP | MP | PKG | Wheel Diameter | Arbor UNC | Flange Shoulder | No Load RPM | Amp | Cord | | |
|---------------|----|----|-----|--|-----------|-----------------|-------------|------|--------|------|---------|
| | | | | | | | | | Length | AWG | Listing |
| W50044 | 1 | 10 | CBX | 4-1/2" | 5/8"-11 | 7/8" | 12,000 | 4.4A | 6' | 18/2 | cETL |
| W8698 | 12 | 72 | CRD | Replacement 5/8"-11 Flange Nut & 4-1/2" Wrench Set | | | | | | | |

6 IN. RANDOM ORBIT POLISHER/SANDER

- Oscillating range of 3/8" for a swirl free finish.
- Dial controlled variable speed control and trigger lock for professional results.
- 2 position side handle for right or left hand use.
- ETL listed 5001662

6" hook and loop backing waffle pad, polishing bonnet, applicator pad, terry cloth cover.

W50087A



Includes 6" hook and loop backing pad, 2 sanding discs, polishing bonnet, applicator pad, terry cloth cover, handle, wrench.

| Item # | IP | MP | PKG | Pad Diameter | Spindle Tread | No Load RPM | Amp | Cord | | | |
|----------------|----|----|-----|--------------------------|---------------|-------------|------|--------|------|---------|--|
| | | | | | | | | Length | AWG | Listing | |
| W50087 | 1 | 6 | CBX | 6" | 5/8"-11 | 6,300 | 5.7A | 6' | 18/2 | ETL | |
| W50087A | 6 | 36 | BAG | 3-pc replacement pad set | | | | | | | |

7 IN VARIABLE SPEED SANDER/POLISHER

- 10 amp motor produces 0-4200 no-load RPM.
- Ball bearing motor and built in regulator for long life.
- Variable speed for use with multiple tasks.
- Ergonomic D-handle for left or right hand use.
- ETL listed 5001662

7" hook and loop backing waffle pad, polishing bonnet, applicator pad, terry cloth cover.

W50084A



Includes - 7" hook and loop backing pad, 2 sanding discs, polishing bonnet, applicator pad, terry cloth cover, handle, spanner wrench.

| Item # | IP | MP | PKG | Pad Diameter | Spindle Tread | No Load RPM | Amp | Cord | | | |
|----------------|----|----|-----|--------------------------|---------------|-------------|-----|--------|------|---------|--|
| | | | | | | | | Length | AWG | Listing | |
| W50084 | 1 | 6 | CBX | 7" | 5/8"-11 | 4,200 | 10A | 6' | 18/2 | ETL | |
| W50084A | 6 | 36 | BAG | 3-pc replacement pad set | | | | | | | |