

PT-E110

Easy-to-use industrial labeling tool



Intuitive menus and built-in label application keys help make the PT-E110 easy for just about anyone to create and produce high-quality laminated labels without ever reading a manual. With high resolution text and symbols and exceptional durability, your labels will leave a truly professional touch.

- QWERTY-style keyboard + graphic LCD + cutter
- Up to 20mm per second print speed + serialization
- Compatibility with HGe and TZe laminated tape cassettes
- 4 label sizes from 3.5mm to 12mm wide
- Carrying case + safety wrist strap + full length tape included



Cable



Security Camera



Network/Faceplate



Asset Management

P-touch
EDGE

brother
at your side

Technical Specifications

Model	PTE110
Type of Printer	Industrial Handheld Labeling System
Print Technology	Laminating Thermal Transfer
Print Resolution	180 dpi
Print Width	.35" (9mm) – 64 dots
Print Speed	Up to 0.78 ips (20mm/sec) – HGe, TZe Tape
Lines per Label	Up to 2 Lines
Rotated Characters	Up to 7 Alpha-Numeric Characters (12mm tape)
Function Keys	5 (Text Settings, Cable Wrap, Cable Flag, Faceplate, Serialize)
Copy/Serialization	Up to 9 Copies/Up to 50 Alpha or Numeric Character Increments
Display	128x16 Dots Graphic LCD (58mm x 23mm) – 15 Characters x 1 Line
Keyboard	QWERTY Layout/Rubber Keys
Cutter	Manual (one finger press)
Media	HGe & TZe Tapes
Media Sizes (width)	12mm, 9mm, 6mm, 3.5mm
Memory	9 Label Designs (up to 720 characters)
Symbol Library	200 Industrial Symbols
Resident Fonts	1 (Helsinki)
Font Sizes/Styles	5 Sizes/9 Styles
Power Supply	6 AAA Alkaline/NiMH Batteries (optional), AD-24ES AC Adaptor (optional)
Dimensions/Weight	4.4" x 2.3" x 8.0" (w x h x d)/0.88 lbs. (w/o tape and batteries)
Contents	PTE110, Carry Case, Wrist Strap, TZeFX221 Tape (8m)
Warranty	2-Year Limited Exchange Warranty



PT-E110 Kit Contains

- Carrying case for PTE110, optional AC adapter and extra tapes.
- 9mm black on white flexible ID tape, full length (8m)
- Wrist safety strap for working at heights



Accessories

- Adapter (AD-24ES AC adapter)
- TC-4 user replaceable cutter blade



Tapes

- Compatible with HGe and TZe tapes
- Visit www.EDGE-Tapes.com to find the right cassette for your job



Abrasion
Resistance



Fade
Resistance



Chemical and
Water Resistant



Laminated Tape
Adhesive Strength



Extreme
Temperature Tested



All HGe, extra-strength
adhesive, flexible ID
and tamper evident
tapes are UL certified

800-543-6144
mobilesales@brother.com
www.brothermobilesolutions.com

Brother is a trademark or registered trademark of Brother Industries, Ltd. in the United States.
All other trademarks and registered trademarks are the properties of their respective companies.
© 2017 Brother Mobile Solutions, Inc. 11030 Circle Point Road, Suite 100, Westminster, CO 80020

brother
at your side