

100-PC SOCKET & BIT SET

- Magnetic bit driver and 22 1" bits with holders,16 hex keys on rings
- Storage / carrying case.

Item #	ΙP	MP	PKG
W1198	1	5	CBX

	Drive		Sockets	
	1/4"	6pt	5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8", 4, 4.5, 5, 5.5, 6, 6.5, 7, 8, 9, 10mm	
	3/8"	6pt	3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4", 10, 11, 12, 13, 14, 15, 17 18mm	3/8" Dr. 3" extension, 3/8" Dr. U-joint
		Deep	3/8, 7/16, 1/2, 9/16", 10, 11, 12, 13mm	3/8" (F) to 1/4" (M) adapter 1/2" (F) to 3/8" (M) adapter
	1/2"	6pt	15/8, 11/16, 3/4, 13/16, 7/8", 14, 15, 17, 18, 19mm	3/8" Dr. 39 gear teeth 6" ratchet, 1/2" Dr. 39 gear teeth 8" ratchet
			Phillips: #1, #2, #3	Pozi: #1, #2, #3
	1" Bits		Slotted: 5/32, 3/16, 1/4,	Star: T15, T20, T25, T27, T30, T40
			7/32, 9/32, 5/16"	Hex: 5/32, 3/16, 7/32, 1/4"
	Hex I	Keys	1/16, 5/64, 3/32, 1/8, 5/32, 3/ ⁻	16, 7/32, 1/4", 1.5, 2, 2.5, 3, 4, 5, 5.5, 6mm

85-PC SOCKET SET

- Drop forged chrome plated carbon steel.Wide range of SAE and Metric sockets in 3 drive sizes.
- Ratchet, extension bar, 1/4" spinner handle, spin disc, spark plug socket, adapter and hex keys.
- Sturdy blow molded case.

Item #	IP	MP	PKG
W1183	1	5	SLV

	Drive		Sockets		000
	1/4"	6pt	5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 13/32, 7/16, 15/32, 1/2, 17/32, 9/16". 4, 4.5, 5, 5.5, 6, 6.5, 7, 8, 9, 10, 11, 12, 13, 14mm	- 3/8" Dr. 3" extension.	
	8pt		1/4, 5/16, 3/8"	•	" (M) adapter
	3/8"	6pt	7/16, 15/32, 1/2, 9/16, 5/8, 11/16" 11, 12, 13, 14, 15, 17mm	3/8" Dr. 39 gear teeth 6" ratchet, 3/8" Dr. 5/8" spark plug socket	
	1/2"	6pt	11/16, 3/4, 13/16, 7/8	1/2" Dr. 39 ge	ear teeth 8" ratchet
1" Bits		its	Phillips: #0, #1, #2 Slotted: 5/32, 3/16, 1/4" Star: T15, T20, T30	Hex Keys	1/16, 5/64, 3/32, 1/8, 5/32, 3/16, 1/4, 5/16, 3/8", 1.5, 2, 2.5, 3, 4, 5, 6, 8,10mm



Products