

# Flashni - Sounder with Xenon Beacon



The Flashni is an audible and visual device which requires one single installation point. This greatly reduces installation costs and is less obtrusive than two separate devices. Versions are available with the sounder and beacon linked, or with separate terminals for independent operation.



## Technical Specification

Voltage	9 - 15Vdc (12V version) 18 - 28Vdc (24V version) (*1)
Current	110mA 12V version (Typical Tone 5) 68mA 24V version (Typical Tone 3)
Sound Output	103dB(A) 12V version (Typical Tone 5) 101dB(A) 24V version (Typical Tone 3)
Tones	Pre-set to tone 5 (12v) Pre-set to tone 3 (24v) (versions are available with user selectable tones)
Flash Power	0.7j
Flash Rate	1Hz
Volume Control	10dB
Monitoring	Reverse polarity
Temperature	- 10°C to + 55°C
Protection	IP54 (s)* IP65 (d)*
Construction	ABS, PC lens
Weight	0.33Kg
Colours	Red or white
Lens Colour	Red, amber, blue, green or clear

(s)\* Shallow Base  
(d)\* Deep / U Base



### Features

- High output sounder beacon
- 12V, 24V and mains module option
- Choice of lens colour options
- Automatic sounder synchronisation

### Benefits

- Up to 103dB(A) with built in Xenon flash
- For use on Fire, Industrial or Security systems
- Suitable for a variety of application
- Improved tone clarity, reducing confusion

Reference	Catalogue No.	Description
FL/RL/R/S SWITCH	640025FULL-0061X	Flashni Sounder/Beacon, Red lens, Red body, Shallow base, Tone select switch.
FL/RL/R/D SWITCH	640031FULL-0111X	Flashni Sounder/Beacon, Red lens, Red body, Deep base, Tone select switch.
FL/AL/W/D SWITCH	640024FULL-0060X	Flashni Sounder/Beacon, Amber lens, White body, Deep base, Tone select switch
FL/RL/R/S 12V SND5	640204FULL-0067	Flashni 12V Sounder/Beacon, Red lens, Red body, Shallow base, tone 5
FL/RL/W/S 12V SND5	640202FULL-0039	Flashni 12V Sounder/Beacon, Red lens, White body, Shallow base, tone 5
FL/CL/W/D 12V SND5	640206FULL-0089	Flashni 12V Sounder/Beacon, Clear lens, White body, Deep base, tone 5

For full list of part numbers, turn to page 61

PRODUCT NAME	PAGE	PRODUCT REFERENCE	CATALOGUE NUMBER	DESCRIPTION
<b>SOLISTA MAXI</b>	19	SOLX/RF/RL/R/S	811021FULL-0037	Solista Maxi Red Body Red Flash Shallow Base (red lens)
		SOLX/RF/RL/R/D	811020FULL-0036	Solista Maxi Red Body Red Flash Deep Base (red lens)
		SOLX/RF/CL/R/S	811041FULL-0006	Solista Maxi Red Body Red Flash (clear lens)
		SOLX/RF/CL/W/S	811023FULL-0039	Solista Maxi White Body Red Flash Shallow Base (clear lens)
		SOLX/RF/RL/W/D	811024FULL-0040	Solista Maxi White Body Red Flash Deep Base (clear lens)
<b>SOLISTA LX WALL</b>	20	812007FULL-0108X	SOL-LX-W/WF/R1/S	Solista LX Wall, Red Body, White Flash, Shallow Base
		812008FULL-0109X	SOL-LX-W/WF/R1/D	Solista LX Wall, Red Body, White Flash, Deep Base
		812009FULL-0110X	SOL-LX-W/WF/R1/U	Solista LX Wall, Red Body, White Flash, U Base
		812010FULL-0111X	SOL-LX-W/WF/W1/S	Solista LX Wall, White Body, White Flash, Shallow Base
		812011FULL-0112X	SOL-LX-W/WF/W1/D	Solista LX Wall, White Body, White Flash, Deep Base
		812012FULL-0113X	SOL-LX-W/WF/W1/U	Solista LX Wall, White Body, White Flash, U Base
		812013FULL-0114X	SOL-LX-W/RF/R1/S	Solista LX Wall, Red Body, Red Flash, Shallow Base
		812005FULL-0107X	SOL-LX-W/RF/R1/D	Solista LX Wall, Red Body, Red Flash, Deep Base
		812014FULL-0115X	SOL-LX-W/RF/R1/U	Solista LX Wall, Red Body, Red Flash, U Base
		812015FULL-0116X	SOL-LX-W/RF/W1/S	Solista LX Wall, White Body, Red Flash, Shallow Base
		812016FULL-0117X	SOL-LX-W/RF/W1/D	Solista LX Wall, White Body, Red Flash, Deep Base
812017FULL-0118X	SOL-LX-W/RF/W1/U	Solista LX Wall, White Body, Red Flash, U Base		
<b>SOLISTA LX CEILING</b>	21	812020FULL-0121X	SOL-LX-C/WF/W1/S	Solista LX Ceiling, White Body, White Flash, Shallow Base
		812021FULL-0122X	SOL-LX-C/WF/W1/D	Solista LX Ceiling, White Body, White Flash, Deep Base
		812022FULL-0123X	SOL-LX-C/RF/W1/S	Solista LX Ceiling, White Body, Red Flash, Shallow Base
		812023FULL-0124X	SOL-LX-C/RF/W1/D	Solista LX Ceiling, White Body, Red Flash, Deep Base
<b>RoLP SOLISTA</b>	22	ROLPSB/SV/RL/R/S	8210112FULL-0015X	RoLP SB, Red LED Beacon, Red lens, Red body, Shallow base
		ROLPSB/SV/RL/R/D	8210113FULL-0016X	RoLP SB, Red LED Beacon, Red lens, Red body, Deep base
		ROLPSB/SV/RL/W/S	8210114FULL-0017X	RoLP SB, Red LED Beacon, Red lens, White body, Shallow base
		ROLPSB/SV/RL/W/D	8210115FULL-0018X	RoLP SB, Red LED Beacon, Red lens, White body, Deep base
		ROLPSB/SV/RL/R/N	8210111FULL-0004X	RoLP SB/Red LED Beacon, Red lens, Red body, No base
		ROLPSB/SV/AL/W/D	8210125FULL-0007X	RoLP SB, Amber LED Beacon, Amber lens, White body, Deep base
<b>RoLP MAXI SOLISTA</b>	23	ROLPX/SB/RL/R/S	8210119FULL-0001	RoLP Maxi Sounder Beacon, Red LED Beacon, Red body, Shallow base
		ROLPX/SB/RL/R/D	8210130FULL-0002	RoLP Maxi Sounder Beacon, Amber lens, White body, Deep base
		ROLPX/SB/RL/R/U	8210121FULL-0003	RoLP Maxi Sounder Beacon, Red LED Beacon, Red Body, U Base
<b>FLASHNI 24V</b>	24	FL/RL/R/S SWITCH	640025FULL-0061X	Flashni Sounder/Beacon, Red lens, Red body, Shallow base, Tone select switch.
		FL/RL/R/D SWITCH	640031FULL-0111X	Flashni Sounder/Beacon, Red lens, Red body, Deep base, Tone select switch.
		FL/AL/W/D SWITCH	640024FULL-0060X	Flashni Sounder/Beacon, Amber lens, White body, Deep base, Tone select switch
		FL/RL/W/D SEPARATE SWITCH	640451FULL-0208X	Flashni Sounder/Beacon, Red Lens, White body, Deep base, Tone select switch, Separate conns for sounder and beacon
		FL/AL/R/D SEPARATE SWITCH	640454FULL-0296X	Flashni Sounder/Beacon, Amber Lens, Red body, Deep base, Tone select switch, Separate conns for sounder and beacon
<b>FLASHNI 12V</b>	24	FL/RL/R/S 12V SND5	640204FULL-0067	Flashni 12V Sounder/Beacon, Red lens, Red body, Shallow base, tone 5
		FL/RL/W/S 12V SND5	640202FULL-0039	Flashni 12V Sounder/Beacon, Red lens, White body, Shallow base, tone 5
		FL/BL/W/D 12V SND5	640203FULL-0068	Flashni 12V Sounder/Beacon, Blue lens, White body, Shallow, tone 5
		FL/CL/W/D 12V SND5	640206FULL-0089	Flashni 12V Sounder/Beacon, Clear lens, White body, Deep base, tone 5
		FL/BL/W/D 12V SND5	640203FULL-0068	Flashni 12V Sounder/Beacon, Blue lens, White body, Deep base, tone 5
		FL/RL/R/S 12V Switch	640023FULL-0058	Flashni 12V Sounder/Beacon, Red lens, Red body, Shallow base, Tone select switch
<b>RoLP LX WALL</b>	25	8500022FULL-0022X	ROLP/W1/LX-W/WF	RoLP LX Wall, White Body, White Flash
		8500023FULL-0023X	ROLP/R1/LX-W/WF	RoLP LX Wall, Red Body, White Flash
		8500024FULL-0024X	ROLP/W1/LX-W/RF	RoLP LX Wall, White Body, Red Flash
		8500025FULL-0025X	ROLP/R1/LX-W/RF	RoLP LX Wall, Red Body, Red Flash
<b>RoLP MAXI LX WALL</b>	25	8500027FULL-0027X	ROLPX/W1/LX-W/WF	RoLP Maxi LX Wall, White Body, White Flash
		8500028FULL-0028X	ROLPX/R1/LX-W/WF	RoLP Maxi LX Wall, Red Body, White Flash
		8500029FULL-0029X	ROLPX/W1/LX-W/RF	RoLP Maxi LX Wall, White Body, Red Flash
		8500030FULL-0030X	ROLPX/R1/LX-W/RF	RoLP Maxi LX Wall, Red Body, Red Flash