



### Slim Line Needle Nose Pliers



- Slim line needle nose pliers
- For use between tightly spaced components
- NN54V, NN55V feature serrated jaws
- NN54G, NN55G feature smooth jaws
- Features green cushion grips

| Catalog Number | UPC Number   | Packed | Length (inch) | Length (mm) | A (inch) | A (mm) | B (inch) | B (mm) | C (inch) | C (mm) | E (inch)    | E (mm)  | Pack weight (lb) | Pack weight (g) | Shelf pack |
|----------------|--------------|--------|---------------|-------------|----------|--------|----------|--------|----------|--------|-------------|---------|------------------|-----------------|------------|
| <b>NN54V</b>   | 043127089499 | Bagged | 5             | 125         | 1 3/16   | 30     | 7/16     | 11     | 9/32     | 7      | 5/64 x 1/16 | 2 x 1.6 | .96              | 435             | 6          |
| <b>NN54GV</b>  | 037103129130 | Bagged | 5             | 125         | 1 3/16   | 30     | 7/16     | 11     | 9/32     | 7      | 5/64 x 1/16 | 2 x 1.6 | .96              | 435             | 6          |
| <b>NN55V</b>   | 037103129468 | Bagged | 5 1/2         | 138         | 1 11/16  | 43     | 15/32    | 12     | 1/4      | 6      | 5/64 x 1/16 | 2 x 1.6 | 1.32             | 5.99            | 6          |
| <b>NN55G</b>   | 043127170935 | Bagged | 5 1/2         | 138         | 1 11/16  | 43     | 15/32    | 12     | 1/4      | 6      | 5/64 x 1/16 | 2 x 1.6 | 1.32             | 5.99            | 6          |


### Fine Point Needle Nose Pliers



- Fine point needle nose pliers
- Positive gripping of fine wires or subminiature components
- Long, thin nose with fine serrated jaws
- Accu-Lite handles (see page 43)

| Catalog Number | UPC Number   | Packed | Length (inch) | Length (mm) | A (inch) | A (mm) | B (inch) | B (mm) | C (inch) | C (mm) | E (inch)    | E (mm)  | Pack weight (lb) | Pack weight (g) | Shelf pack |
|----------------|--------------|--------|---------------|-------------|----------|--------|----------|--------|----------|--------|-------------|---------|------------------|-----------------|------------|
| <b>ENN54</b>   | 043127170904 | Bagged | 6 1/2         | 163         | 1 3/16   | 30     | 7/16     | 11     | 9/32     | 7      | 5/64 x 1/16 | 2 x 1.6 | .96              | 435             | 6          |

### Long Nose Wiring and Pick-up Pliers



- Wiring and pick-up pliers
- With alignment pin
- Long nose design
- Features green cushion grips
- Serrated jaws

| Catalog Number  | UPC Number   | Packed | Length (inch) | Length (mm) | A (inch) | A (mm) | B (inch) | B (mm) | C (inch) | C (mm) | E (inch)    | E (mm)  | Pack weight (lb) | Pack weight (g) | Shelf pack |
|-----------------|--------------|--------|---------------|-------------|----------|--------|----------|--------|----------|--------|-------------|---------|------------------|-----------------|------------|
| <b>LN774512</b> | 043127063077 | Bagged | 5 1/2         | 138         | 1 3/4    | 45     | 15/32    | 12     | 1/4      | 6      | 5/64 x 1/16 | 2 x 1.5 | 1.08             | 490             | 6          |