

1572 ESD Krafftform Micro screwdriver for Microstix screws, m x 40 mm

ESD Series



EAN:	4013288181169	Size:	157x13x13 mm
Part number:	05030080001	Weight:	13 g
Article number:	1572 ESD	Country of origin:	CZ
		Customs tariff number:	82054000



- Screwdriver for Microstix® screws
- ESD-safe tool thanks to surface resistance of $< 10^9 \text{ Ohm}$
- Hexagonal anti-roll feature against rolling away
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Ergonomic Krafftform handle for pleasant and low-fatigue working

ESD-safe screwdriver for Microstix screws. Dependable protection against electrostatic energy and associated damage. Come with an ergonomic Krafftform handle for pleasant and low-fatigue working and Black Point tip for high corrosion protection.

Web link

http://products.wera.de/en/screwdrivers_esd_series_1572_esd.html

Wera - 1572 ESD
05030080001 - 4013288181169

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

ESD Series

Wera ESD Tools



The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

High protection




The electric surface resistance of the Wera ESD material is $\leq 10^9$ ohm. This securely protects components against electrostatic energy and associated damage.

Kraftform Micro Handle



Multi-component screwdriver handle for ergonomic working.

The power zone



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The precision zone




The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The fast-turning zone




The fast-turning zone just below the rotating cap allows rapid twisting.

Rotating cap and fast-turning zone



The fast-turning zone just below the rotating cap allow rapid twisting. This makes time-consuming grip adjustments as with other conventional precision screwdrivers unnecessary.

Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.

Web link

http://products.wera.de/en/screwdrivers_esd_series_1572_esd.html

Wera - 1572 ESD

05030080001 - 4013288181169

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Further versions in this product family:



mm



mm



mm



inch

05030080001	m	40	97	2.5	1 9/16
05030081001	00	40	97	2.5	1 9/16
05030082001	F	40	97	2.5	1 9/16
05030083001	0	40	97	2.5	1 9/16
05030084001	1	40	97	2.5	1 9/16

Web link

http://products.wera.de/en/screwdrivers_esd_series_1572_esd.html

Wera - 1572 ESD

05030080001 - 4013288181169

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de