

Zyklus Mini



| | | | |
|------------------------|------------------|-------------------------------|---------------|
| EAN: | 4013288182180 | Size: | 200x105x60 mm |
| Part number: | 05135918001 | Weight: | 566 g |
| Article number: | KK Zyklus Mini 2 | Country of origin: | CZ |
| | | Customs tariff number: | 82041100 |

- Drop-forged, full-steel ratchet design
- For screwdriving in very confined working situations
- Zyklus sockets 8790 FA for direct insertion in the Zyklus Mini 2
- Bit holder, 9 sockets, 14 bits and 1 adaptor
- In robust textile box

Ratchets and screws in a Kraftform Kompakt format. These drop-forged, full-steel ratchets, Zyklus Mini 1 and 2, combine filigree design with incredible robustness. For particularly rapid screwdriving in confined working situations. Zyklus Mini 1 or Zyklus Mini 2 can be used whenever screwdriving with power tools or conventional hand tools is unfeasible for lack of space. 1 bit ratchet Zyklus Mini 1; suitable for the take-up of bits with 1/4" hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3 and Wera connecting series 1 and 4; also possible to use 1/4" sockets by attaching the Wera adaptor 870/1. 1 socket ratchet Zyklus Mini 2; suitable for the direct attachment of Wera Zyklus special sockets 8790 FA.

Web link
http://products.wera.de/en/zyklus_ratchets_and_accessories_zyklus_mini_kk_zyklus_mini_2.html

Wera - KK Zyklus Mini 2
 05135918001 - 4013288182180

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Zyklus Mini

Set contents:



8001 A

- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0
- 05073999001 1 x 1/4"x87.0



8005

- 05003660001 1 x 107



813

- 05051274001 1 x 1/4"x78



870/1

- 05136000001¹⁾ 1 x 1/4"x25

1) With friction ball; for manual nut spinner sockets



851/1 Z PH

- 05072070001 1 x PH 1x25
- 05072072001 1 x PH 2x25



855/1 Z PZ

- 05072080001 1 x PZ 1x25
- 05072082001 1 x PZ 2x25



867/1 TORX®

- 05066485001 1 x TX 10x25
- 05066486001 1 x TX 15x25
- 05066487001 1 x TX 20x25
- 05066488001 1 x TX 25x25
- 05066490001 1 x TX 30x25
- 05066491001 1 x TX 40x25



840/1 Z Hex-Plus

- 05056315001 1 x 3.0x25
- 05056320001 1 x 4.0x25
- 05056325001 1 x 5.0x25
- 05056330001 1 x 6.0x25



8790 FA

- 05003665001 1 x 4.0
- 05003667001 1 x 5.0
- 05003668001 1 x 5.5
- 05003669001 1 x 6.0
- 05003670001 1 x 7.0
- 05003675001 1 x 8.0
- 05003690001 1 x 10.0
- 05003684001 1 x 12.0
- 05003685001 1 x 13.0

Web link

http://products.wera.de/en/zyklus_ratchets_and_accessories_zyklus_mini_kk_zyklus_mini_2.html

Wera - KK Zyklus Mini 2
05135918001 - 4013288182180

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Zyklus Mini

The Zyklus Mini Ratchets



Combines elegant design with incredible resilience. Suitable for rapid fastening even in confined working situations. The Wera Zyklus Mini is applied whenever fastening with a power tool or conventional tools is impossible due to insufficient space. The Zyklus Mini 1 for the direct attachment of bits; the Zyklus Mini 2 for the direct attachment of the special Wera Zyklus sockets.



For all difficult-to-access applications.

Small return angle



The fine tooth mechanism, with its 60 teeth, allows a small return angle of only 6° – ideal for precision work.

Is rapid screwdriving possible with the Zyklus Mini?



High working speeds can be attained with the Zyklus Mini. The thumb wheel is important, enabling more rapid screwdriving, and the Zyklus Mini handle only needs to be used for the final tightening of the screw.

Slim design



Its slim design makes it ideal for all particularly confined working situations.

Is such a small tool sufficiently resilient?




The Zyklus Mini 1 can withstand at least 65 Nm. That is far more power than can normally be transferred to such a small tool.

What parts can be connected to the Zyklus Mini 1?



Bits and sockets. Bits can be connected directly. However, a holder can be connected first and then the bit can be attached to this. This then serves as an extension with a free-turning sleeve. An adaptor e.g. Wera 870/1 is needed for sockets – 1/4" hexagonal on a square drive (included in the Bit-Check and with the individual Zyklus Mini 1 in the set).

Zyklus Mini 2



The Zyklus Mini 2 is suitable for the direct attachment of the special Wera Zyklus sockets 8790 FA. These sockets feature a very low height, ideal for confined working spaces.

Web link

http://products.wera.de/en/zyklus_ratchets_and_accessories_zyklus_mini_kk_zyklus_mini_2.html

Wera - KK Zyklus Mini 2
05135918001 - 4013288182180

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de