

**A-series
ZQV 4N/2**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

General ordering data

| | |
|------------|----------------------------|
| Type | ZQV 4N/2 |
| Order No. | 1527930000 |
| GTIN (EAN) | 4050118332766 |
| Qty. | 60 pc(s). |

**A-series
ZQV 4N/2**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

| | | | |
|------------|----------|-----------------|-----------|
| Width | 9.9 mm | Width (inches) | 0.39 inch |
| Height | 2.8 mm | Height (inches) | 0.11 inch |
| Depth | 27.95 mm | Depth (inches) | 1.1 inch |
| Net weight | 1.371 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |
|----------------------------------|--------|----------------------------------|--------|

Material data

| | | | |
|---------------------------|-------|--------|--------|
| Material | Wemid | Colour | Orange |
| UL 94 flammability rating | V-0 | | |

Additional technical data

| | | | |
|--------------------------|-----|----------------|---------|
| Explosion-tested version | Yes | Type of fixing | Plugged |
|--------------------------|-----|----------------|---------|

Dimensions

| | |
|-----------------|--------|
| Pitch in mm (P) | 6.1 mm |
|-----------------|--------|

Rating data

| | |
|---------------|------|
| Rated current | 32 A |
|---------------|------|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 6.0 | EC000489 | eClass 6.2 | 27-14-11-40 |
| eClass 8.1 | 27-14-11-40 | eClass 9.0 | 27-14-11-40 |
| eClass 9.1 | 27-14-11-40 | | |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|--|
| Brochure/Catalogue | CAT 1 TERM 16/17 EN |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| Engineering Data | STEP |
| User Documentation | 2434520000_BED-ANL.ZQV_A_REIHE.pdf |