

## Applications:

Connect sources and display in the most efficient cost effective way.

## Ideal use:

High end 4K home AV systems. Corporate board rooms. Education facilities



Use the new SY HDMI links to ensure the most accurate and reliable connection

See Also:  
HDBT 18G70  
HDBT 70SE Slim Edge  
HDBT 100 Slim  
HDBT ARC100


## The SY HDBT-EC HDBaseT set

- **Cost effective connection for high quality video**  
Miniature size makes it an ideal companion for managing connections to projectors and AV receivers.  
**Transmit 4K and HD up to 70m**  
Easy quick connection for commercial and residential applications enabling transmission of the highest quality Video. 4K up to 40m. HD up to 70m.
- **Great value the highest build quality**  
The highest quality robust power supply utilising Bi-directional PoC.
- **Compact. Light. Easy to conceal**  
Designed to support the latest slim generation of displays. Only 16mm tall.
- **SY's legendary build quality and reliability**

**Just one of many innovative unique solutions SY is offering installers and integrators across the UK and the EMEA**

### SY HDBaseT extenders

Great value. 4K and HD. IR control  
Connect and control sources and displays  
**HDBT-70EC**



- HDMI
- IR
- Power
- CATx

**Core range.**  
**Great performance high value.**  
**Robust build.**  
**4K UHD.**

**Connect. Switch. Scale. Control.**

# Data Sheet

## SY HDBT-EC Tx/RX set

MODEL NAME:	SY HDBT-EC
PART NUMBER:	SY-HDBT-EC-Set

SPECIFICATIONS			
Video Resolution/formats (applies to Tx and Rx)		VESA and SMPTE 480p to 2160p (4K UHD) with 3D. (All resolutions to: Supports 3840x2160p @60Hz 4:4:4 8bit, 3840x2160p @30Hz 4:4:4 8bit) All PC resolutions to 1920x1200	
Bandwidth		10.2Gbps	
HDCP		Supports all version up to 2.2v	
Tx			
INPUTS	Input	1x HDMI type A 1.4v	
	IR	1x 3.5mm	
OUTPUT	HDBaseT	1x RJ45	
	IR	1X 3.5MM	
Rx			
INPUTS	HDBaseT	1x RJ45	
	IR	1x 3.5mm	
OUTPUT	IR	1x 3.5mm	
	HDMI	1x HDMI type A 1.4v	
RANGE			
		HD/1080p	70m
		4K	40m (@30Hz 4:4:4 8bit)
POWER SUPPLY		12V DC /1A	
OPERATING TEMP		0 – 45 °C non-condensing	
WEIGHT AND DIMENSIONS			
Weight (net)		0.240 Kg (Each)	
Size (WHD)		120 x 16 x 74 mm (Each)	

WHAT'S IN THE BOX	
1x HDBT CE Tx	
1x HDBT CE Rx	
1x UK / EU wall power supply	
1x IR Receiver	
1x IR Emitter	
2x mounting brackets and screws	

