



|                        |                                  |                               |               |
|------------------------|----------------------------------|-------------------------------|---------------|
| <b>EAN:</b>            | 4013288168344                    | <b>Size:</b>                  | 155x100x30 mm |
| <b>Part number:</b>    | 05073670001                      | <b>Weight:</b>                | 162 g         |
| <b>Article number:</b> | Kraftform Kompakt Micro 11 ESD 1 | <b>Country of origin:</b>     | CZ            |
|                        |                                  | <b>Customs tariff number:</b> | 82079030      |

- Bit holder suitable for the take-up of bits with 4 mm halfmoon or HIOS drive
- ESD-safe tool thanks to surface resistance of  $< 10^9$  Ohm
- Holder with anti-roll feature, swivel cap and quick-release chuck
- Suitable for bits with 4 mm halfmoon and 4 mm HIOS drive
- In a practical pouch

Kraftform Kompakt Micro set for precision mechanical work. Suitable for the take-up of bits with 4 mm halfmoon drive (Wera series 9) and bits with 4 mm HIOS drive (Wera series 21). Electrical surface resistance of  $< 10^9$  Ohm for secure protection against electrostatic charge. Manufactured in accordance with DIN EN 61340-5-1. Compact handle/interchangeable blade system for fast blade change. Kraftform Micro handle with twist cap and free-turning zone for rapid twisting, making any time-consuming repositioning of the fingers unnecessary. Power zone with integrated soft zones for the transfer of higher tightening and loosening torque. Precision zone directly above the blade for the right angle for adjustment work. Bits for manual as well as power tool operations. Rapid fixing of the bit: just push the bit into the insert for automatic locking and a secure fit. To change the bit, simply push the sleeve forward and remove. Free-turning sleeve for simple guidance of the tool during the screwdriving process. Bits suitable for manual as well as power tool operations with electric screwdrivers (e.g. HIOS, Delvo, Sehan). Applications for example on smartphones, cell phones, cameras, electrical appliances, in dental labs and dental surgeries.

**Web link**

[http://products.wera.de/en/screwdrivers\\_esd\\_series\\_kraftform\\_kompakt\\_micro\\_11\\_esd\\_1.html](http://products.wera.de/en/screwdrivers_esd_series_kraftform_kompakt_micro_11_esd_1.html)

Wera - Kraftform Kompakt Micro 11 ESD 1  
05073670001 - 4013288168344

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

## ESD Series

### Set contents:



**1013 Kraftform Micro ESD**  
05300004001 1 x 97  
05300004001 1 x 97



**851/9 C**  
05135270001<sup>1)</sup> 1 x PH 00x44  
05135274001<sup>2)</sup> 1 x PH 0x44  
05135276001<sup>1)</sup> 1 x PH 1x44

1) Optimised for Asian PH screws  
2) Size 0 modified according to JCIS 0 (Japanese Camera Industrial Standard)



**867/9 C TORX®**  
05345351001 1 x TX 5x44  
05345350001 1 x TX 6x44



**800/9 C**  
05135265001 1 x 0.23x1.5x44  
05135266001 1 x 0.40x2.0x44  
05135267001 1 x 0.50x3.0x44



**840/9 C**  
05135268001 1 x 1.5x44  
05135269001 1 x 2.0x44

### Wera ESD Tools



In a practical pouch




The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

### High protection



The electric surface resistance of the Wera ESD material is  $\leq 10^9$  ohm. This securely protects components against electrostatic energy and associated damage.

### For Halfmoon and HIOS Bits



Features a combination bitholder for both bits with Halfmoon and bits with HIOS drive.

### Web link

[http://products.wera.de/en/screwdrivers\\_esd\\_series\\_kraftform\\_kompakt\\_micro\\_11\\_esd\\_1.html](http://products.wera.de/en/screwdrivers_esd_series_kraftform_kompakt_micro_11_esd_1.html)

Wera - Kraftform Kompakt Micro 11 ESD 1  
05073670001 - 4013288168344

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

**Kraftform Micro Handle**




Multi-component screwdriver handle for ergonomic working.

**The precision zone**



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

**The power zone**



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

**Rotating cap and fast-turning zone**



The fast-turning zone just below the rotating cap allow rapid twisting. This makes time-consuming grip adjustments as with other conventional precision screwdrivers unnecessary.

**Web link**

[http://products.wera.de/en/screwdrivers\\_esd\\_series\\_kraftform\\_kompakt\\_micro\\_11\\_esd\\_1.html](http://products.wera.de/en/screwdrivers_esd_series_kraftform_kompakt_micro_11_esd_1.html)

Wera - Kraftform Kompakt Micro 11 ESD 1  
05073670001 - 4013288168344

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)