

NEBO
the **Larry BOSS**
3 IN ONE POWER WORK LIGHT

The Larry® BOSS, the essential 3-in-1 power work light, features a high-power flashlight, work light and red light. Taking charge of keeping your work space clean, the BOSS is equipped with a recessed 13.5" telescopic magnetic grabber, great for picking up loose screws, nails, nuts and bolts. The Larry® BOSS also has a powerful magnetic base for hands-free lighting.



4 LIGHT MODES

- Top light (120 lumens) - 12 hours / 44 meters
- Work light (400 lumens) - 4.5 hours / 27 meters
- Red light (40 lumens) - 20 hours / 7 meters
- Red hazard flasher - 40 hours

DESIGN

- Fully dimmable
- Anodized aircraft-grade aluminum; water and impact-resistant
- Powerful magnetic base
- 13.5" telescoping magnetic grabber
- Rubberized slide release for magnetic grabber

OPERATION


- Front-positioned, ON/OFF button

BATTERIES

- Powered by 3 AA batteries (included)

SPECS

- 0.8 lbs.
- Length: Compacted: 7.625" / Extended: 22.375"
- Width: 1.1875" / Depth: 1.375"



Display Dimensions

(H) 15.5" x (W) 5.5" x (D) 7.75"

Gift Box Dimensions

(H) 7.75" x (W) 1.5625" x (D) 1.325"

UPC CODE	ITEM	DESCRIPTION
645397930860	6431	Larry® BOSS Power C·O·B Work Light

NEBO
the **BIG Larry PRO**
POWER WORK LIGHT



The **BRIGHTEST Larry yet...**The BIG Larry® PRO features a high-power, **500 lumen** C·O·B work light and red hazard flasher. **Fully rechargeable** and equipped with 2 magnetic charging stations, the BIG Larry® PRO is ready to handle any task at any time. The PRO also has a powerful magnetic base and adjustable steel clip for convenient hands-free lighting. When there is work to be done...bring a PRO!



3 LIGHT MODES

- HIGH (500 lumens) - 4.5 hours / 37 meters
- Red (45 lumens) - 8 hours / 13 meters
- Red hazard flasher - 24 hours / 13 meters

DESIGN

- Fully dimmable
- Direct-to-Red
- Anodized aircraft-grade aluminum; water and impact-resistant
- Adjustable clip
- Powerful magnetic base
- Battery charging indicator

OPERATION

- Top-positioned, ON/OFF button

ACCESSORIES




- Two magnetic charging stations and cables

BATTERIES

- Powered by 1 Li-ion rechargeable battery (included) (Recharge time: 5 - 6 hours)

SPECS

- 0.8 lbs.
- (H) 7.75" x (W) 1.1875" x (D) 1.375"



Display Dimensions

(H) 12.75" x (W) 9.5" x (D) 8.75"

Gift Box Dimensions

(H) 7.75" x (W) 1.5625" x (D) 1.325"



CALIFORNIA REQUIRED ⚠️ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov/product

UPC CODE	ITEM	DESCRIPTION
645397931959	6640	BIG Larry® PRO Power Work Light