



Soldering Tips - Weller Compatible

MS SERIES

COMPATIBLE STATIONS:Weller WSL, Weller WSL2, Weller WD1, Weller WD2, Weller WS80, Weller WDS80, Weller WSD81, Weller WSP 80, Weller WPR 80

Plato is one of the largest manufacturers of solder tips in the world, producing tips to fit all of the most popular solder stations. The long life and fast heat recovery of a Plato solder tip increases user effectiveness and decreases production times. All Plato solder tips manufactured since January 2004 are tinned with Lead-Free solder. Plato is the name for reliable soldering supplies.

Long Life: Using a high quality Plato solder tip increases solder speeds and decreases the total cost of manufacture. Higher temperatures and high tin content solders, common in lead-free solder processes, place additional strain on soldering iron tips. The long life of a Plato solder iron tip reduces tip changes, decreasing the total number of tips used and decreasing production time.

Rapid Heat Recovery: Plato solder tips are constructed from highly conductive premium grade copper to transmit heat to the work more quickly than other brands. This quick heat recovery enables more joints to be soldered per minute, thus reducing manufacturing time and costs.




- Fast heat recovering increases soldering speed
- Longer tip reduces manufacturing costs
- Fewer tip change overs

[Request More Info](#)

Product Dimensions


MS-4140 Conical

0.8mm
10 units/case




MS-4120 Point

Cross Reference: Weller LT1
0.25mm
10 units/case




MS-4110 Point, long

Cross Reference: Weller LT1L
0.25mm
10 units/case



MS-4100 Point, micro


0.25mm
10 units/case






MS-5160 Bevel, micro

Cross Reference: Weller LT4W
1.2mm
10 units/case




MS-3125 Angled SMD

Cross Reference: Weller LT4X
0.4mm
10 units/case




MS-3200 Screwdriver

Cross Reference: Weller LTA
1.6mm
10 units/case




MS-3300 Screwdriver

Cross Reference: Weller LTB
2.4mm
10 units/case




MS-3300LF Screwdriver, long-life

Cross Reference: Weller LTB LF
2.4mm
10 units/case




MS-3400 Screwdriver

Cross Reference: Weller LTC
3.2mm
10 units/case




MS-3600 Screwdriver

Cross Reference: Weller LTD
4.6mm
10 units/case




MS-0100 SMD flow tip

Cross Reference: Weller LTGW
2.1mm
10 units/case




MS-3110 Screwdriver

Cross Reference: Weller LTH
0.8mm
10 units/case



MS-3101 Angled SMD


Cross Reference: Weller LTHX
0.6mm
10 units/case






MS-3150 Screwdriver, long

Cross Reference: Weller LTK
1.3mm
10 units/case




MS-3250 Screwdriver, long

Cross Reference: Weller LTL
2.0mm
10 units/case



MS-3450 Screwdriver, long

Cross Reference: Weller LTM
3.2mm
10 units/case



North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
Email: tsales@techspray.com

Europe

ITW Contamination Control
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
Email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2017 Illinois Tool Works