

# GF 3002

## Hot-Melt Adhesive Systems



### GF 3002 Specifications

Item No.	33241
Accessories	sturdy metal stand included
Glue	accepts 1/2" & 7/16" dia. industrial glue sticks within temp range
Operating Temperature	400°F (204°C)
Melting Capacity	high 7.5 gm / minute
Warm Up Time	quick 7 minutes
Nozzle Diameter	0.1" (2 mm)
Net Weight	0.7 lbs (11.4 oz)
Single Sell Pack	dimensions: 10.3" x 6.8" x 1.8" weight: 1.1 lbs (17.6 oz)
Warranty	one year limited
Certifications	cSAus, UL Listed, RoHs Compliant, ISO 9001:2001 Made in E.U.

### GF 3002 Hot-Melt Adhesive Systems

STEINEL's GlueFix™ 3002 represents the state-of-the-art in hot-melt adhesive application. The exclusive PTC (positive temperature control) electronic heating system ensures the ideal bonding temperature for extended periods of time, providing precise, continuous glue output. Industrial users and trades professionals alike count on STEINEL glue guns for consistent high performance and reliability.

### Applications

Packaging, construction, pipe insulation, hobbies, circuit board sealing and paintless dent removal

### Key Features:

- Easy to use, mechanical glue stick feeding system for consistent flow
- Die cast aluminum heating chamber retains heat for increased volume
- No-drip nozzle won't ooze hot glue
- Lightweight 11.4 oz construction for comfortable long term use




Construction



Packaging



Pipe Insulation



Circuit Board Sealing



Paintless Dent Removal



[www.steinell.net](http://www.steinell.net)

### Application Glue Guide

Model	Open Time	ABS	PP / PC / HDPE LDPE	Polystyrene	PVC	Glass Reinforced Plastic	Aluminum Stainless Steel	EPS Foam	Wood	Sand Mold	Glass	Cardboard
GF 232 General	Medium	●	●	●●●	●	●	●	●●●●	●●	●●	●●●	●●●
GF 14 Carton	Fast	●	●	●●	●	●●	●●●	●●	●	●●●●	●	●●●●
GF 23 Wood	Long	●●	●	●●●	●	●●	●●●	●●●	●●●●	●●●●	●	●●●
GF 213 Laminate	Long	●	●	●●●	●●●	●●	●●●	●●●	●●	●●	●	●●●
HG 260 Hi Strength	Long	●●●	●	●●●	●●	●●●	●●●	●●	●●●●	●	●●●	●●●

Key: ● Poor ●● Fair ●●● Good ●●●● Very Good

### Accessories for a Variety of Applications



**2 mm Nozzle**  
1.0" x 0.8" x 0.8"  
No. 01247



**2.8 mm Fine Tip Nozzle**  
1.9" x 0.8" x 0.8"  
No. 01245



**1 mm Nozzle**  
1.9" x 0.8" x 1.8"  
No. 01243



**10 mm Small Reflector**  
1.1" x 0.8" x 0.5"  
No. 01241



**G 200C**  
Clear Glue  
No. 04080 - 1 lb  
04801 - 1 kg



**GF 14**  
Carton Glue  
No. 04040 - 1 lb  
04041 - 11 lbs



**GF 23**  
Wood Glue  
No. 04034 - 1 lb  
04035 - 11 lbs



**GF 213**  
Laminate Glue  
No. 04037 - 1 lb  
04038 - 11 lb



**GF 232**  
General Purpose  
No. 04031 - 1 lb  
04032 - 11 lb



**GF 260**  
High Strength  
No. 04043 - 1 lb  
04044 - 11 lbs