

Building Multi-Purpose Systems

Interconnectivity for any application: Plugs, jacks, binding posts

Creating a new studio? Outfitting a mobile broadcast truck? Or maybe a new audio/video system? For all the gear you design or install, you need a wide variety of connection aids. Pomona offers plugs, jacks, and binding posts to fit diverse applications. Whether you're setting up a complex access panel or need a simple banana plug for a monitor. In the shop, lab, studio, or on the road... Pomona keeps you connected with quality.

RCA and banana plugs and jacks


Features

- Do-it-yourself 1/4in (stereo and mono) and RCA plugs and jacks.
- 1/4in to RCA converters to attach two different cable types.
- RCA splitter (f/m/f).

Binding posts

Features

- Dual binding posts have a large diameter cross hole that allows for connections to wires up to 12 AWG.
- Standard 3/4in (19.05mm) spacing allows connection to industry standard dual banana plugs.
- Two styles offered: standard and raised base versions.
- Slotted post heads for fast and secure wire connection.



See following page

for a complete list of multipurpose connectors for broadcast



RCA and banana plugs and jacks

Double Banana Plug, *-0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray and -9 White MDP-*



Do-it-yourself Solderless Stackup Banana Plug with Safety Shield, 10 Per Package, *-0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray and -9 White 1825-*



Dual Binding Posts 6883

Binding posts



Binding Post/Bantam Plug 5001



Dual Binding Posts, Raised Base 6884



Binding Post/Phone Plug 1285



Do-it-yourself Solderless Stackup Banana Plug, 10 Per Package, *-0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray and -9 White 1325-*



Double Banana/Phono Jack 1442



Triple Banana Plug, Black 2970-0 (Black) 2970-2 (Red)

Go to **www.pomonaelectronics.com** for more information

In the United States:

Pomona Electronics 9028 Evergreen Way Everett, WA 98204 United States

www.pomonaelectronics.com

Tel: 1.800.490.2361 Fax: 425.446.5844

In Europe:

Pomona Electronics P.O.Box 1186 5602 BD Eindhoven The Netherlands

www.pomona.cc

Tel: +31 (0) 40 2675 150 Fax: +31 (0) 40 2675 151

All other areas:

www.pomonaelectronics.com

Tel: 1.425.446.5500 Fax: 1.425.446.4806

Copyright © 2004. Pomona is a registered trademark of Pomona Electronics. Specifications subject to change without notice. All rights reserved. Printed in the USA. 5/04 2152227 D-ENG-N Rev. A