


Part Number: [0502128100](#)
 Status: Active
 Description: 2.00mm Pitch Crimp Terminal, Female, 24-30 AWG, Bag

Documents:

3Dモデル	製品仕様書 PS-51160-001 (PDF)
図面 (PDF)	製品仕様書 PS-51160-006-001 (PDF)
製品仕様書 PS-51065-005 (PDF)	製品仕様書 PS-51225-003-001 (PDF)
製品仕様書 PS-51065-016-001 (PDF)	製品仕様書 PS-52968-006-001 (PDF)
製品仕様書 PS-51065-017-001 (PDF)	製品仕様書 PS-52968-007-001 (PDF)
製品仕様書 PS-51065-018-001 (PDF)	製品仕様書 PS-53717-002-001 (PDF)
製品仕様書 PS-51089-001 (PDF)	製品仕様書 PS-54111-002-001 (PDF)
製品仕様書 PS-51089-005-001 (PDF)	製品仕様書 PS-54214-001 (PDF)
製品仕様書 PS-51090-003 (PDF)	製品仕様書 PS-54452-007-001 (PDF)
製品仕様書 PS-51090-004-001 (PDF)	製品仕様書 PS-55533-004-001 (PDF)
製品仕様書 PS-51090-005-001 (PDF)	圧着仕様書 510900001-000 (PDF)
製品仕様書 PS-51090-009 (PDF)	梱包仕様書 SPK-50212-001-001 (PDF)
製品仕様書 PS-51090-016-001 (PDF)	RoHS Certificate of Compliance (PDF)
製品仕様書 PS-51090-017-001 (PDF)	Product Literature (PDF)
製品仕様書 PS-51090-018-001 (PDF)	

一般用途	Signal
Crimp Quality Equipment	有
梱包違い製品	50212-8000 (Reel)
Product Literature Order No	987651-8983
製品名	DuraClik, Mi II, Micro-Latch, Sherlock
UPC	800754369473
機械的性能/材質	
ジェンダー	フィメール
材質 - 金属部	りん青銅
材質 - 嵌合部メッキ	錫
材質 - ターミナルメッキ	錫
Net Weight	20.400/mg
梱包形態	ポリ袋
実装スタイル	圧着またはコンプレッション
被覆外径	1.40mm max.
電線サイズ (AWG)	24, 26, 28, 30
Wire Size mm ²	N/A
電気的性能	
最大定格電流	2.0A
最大定格電圧	125V
参考情報	
図面・仕様書情報	
圧着仕様書	510900001-000
Crimp Specification	CS-50212
梱包仕様書	SPK-50212-001-001
製品仕様書	PS-51065-005, PS-51065-016-001, PS-51065-017-001, PS-51065-018-001, PS-51089-001, PS-51089-005-001, PS-51090-003, PS-51090-004-001, PS-51090-005-001, PS-51090-009, PS-51090-016-001, PS-51090-017-001, PS-51090-018-001, PS-51160-001, PS-51160-006-001, PS-51225-003-001, PS-52968-006-001, PS-52968-007-001, PS-53717-002-001,



EU ELV
Not Relevant

EU RoHS China RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free
Status

Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for
any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[50212 Series](#)

Use With
DuraClik Receptacle Housing [502351](#)

Micro-Latch Receptacle Housing
[51065](#)
Mi II Receptacle Housings
[51089](#) , [51090](#)

PS-54111-002-001, PS-54214-001, PS-54452-007-001,
PS-55533-004-001
SD-50212-001

This document was generated on 09/11/2018
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION