

Part Number: [0039012080](#)
Status: Active
Overview: [Mini-Fit Jr. Power Connectors](#)
Description: Mini-Fit Jr. Receptacle Housing, Dual Row, 8 Circuits, UL 94V-2, Natural

Documents:

3D 모델	Application Specification AS-5557-001-001 (PDF)
도면 (PDF)	Packaging Specification PK-5557-002-000 (PDF)
제품규격 PS-45750-001-001 (PDF)	Test Summary 55570002-TS-000 (PDF)
제품규격 PS-5556-001-001 (PDF)	RoHS 증명서(PDF)
제품규격 TS-5556-002-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

일반적 특성
적용제품
설명

Power, 와이어 대 보드, 와이어 대 와이어
Current = 13A max. per circuit when header is mated to a receptacle loaded with [45750](#) series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.. Glow Wire Equivalent Part.

전체보기
제품명
UPC

[Mini-Fit Jr. Power Connectors](#)
Mini-Fit Jr.
800753644632

물리적 특성
분리형

No

최대 회로수
색상 - Resin

8
Natural

난연성
암수구분

94V-2
리셉터클

Glow-Wire Capable
원재료 - 플라스틱

No
나일론 (PA)

Net Weight
열 수

1.760/g
2

포장타입
패널마운트

백 (Bag)
No

피치 - 결합부
피치 - 터미널 간격

4.20mm
4.20mm

결합제품 오삽입 장치
End-to-End 연결형

Yes
No

사용온도 범위

-40° to +105°C

전기적 특성

전류 - 접촉 당 최대 출력 13.0A

납땜 프로세스 정보

Lead-freeProcess Capability N/A

원재료 정보

Engineering Number 5557-08R

참고 - 도면번호

Application Specification AS-5557-001-001
Packaging Specification PK-5557-002-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit
[Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series
[5557 Series](#)

Mates With

[5559](#) Dual Row, [5566](#) Vertical with Pegs, [5566](#) Vertical without Pegs, [5569](#) Right Angle Dual Row with Flanges, [5569](#) Right Angle Dual Row with Pegs, [43810](#) , [44068](#) , [44281](#) , [87427](#) , [42404](#) , [42440](#)

Use With

[5556](#) Mini-Fit Female Crimp Terminals, [45750](#) Mini-Fit Plus HCS Crimp Terminal

제품규격
도면
Test Summary

PS-45750-001-001, PS-5556-001-001, TS-5556-002-001
SD-5557-003-000
55570002-TS-000

This document was generated on 09/20/2018
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION