

8 in 1 ToughArmor

ICY DOCK®
www.icydock.com

HDD BAY

MB998IP-B • MinisAS HD to 8 Bay 2.5" SAS/SATA
Hard Drive & SSD 5.25" Backplane Cage



SUPPORT
miniSAS HD



2x MiniSAS HD Support 8x Drives



Compatible with
Mini-SAS RAID cards



EAGLE HOOK



Support 7mm drive height



EMI GROUNDING + ANTI-VIBRATION DESIGN

METAL HEAT DISSIPATION



HDD IN

HDD OUT

Drive label for each drive tray



FULL METAL
CONSTRUCTION



Key Features

- Heavy duty full metal construction with commercially designed for medical and military systems, media servers, workstation, HPCs and IPCs, approved & used by Tier 1 companies
- Perfect for rugged applications and complies to flammability requirements
- Fits 8 x 5mm - 7mm 2.5" SATA hard drives or SSD's in a single 5.25" bay for data intensive applications
- Dual 40mm user-controllable fans with setting for high, low ,off
- Connected by 2 x Mini-SAS HD data cables for all 8 bays. for plug-and-play compatibility with most motherboards and RAID cards
- Requires only 2 x 15pin SATA power connectors to power all 8 bays
- Drive label plugs to keep track of your RAID drives
- Anti-Vibration Technology (AVT) - creates a safe environment for hard drives or SSDs
- Active Power Technology (APT) - individual led & cooling fan only powers up if there is a drive installed in the bay
- Eagle-hook lock system keeps drives secured within the enclosure
- Removable tray system for easy maintenance
- Supports SAS 12Gbps (single channel) & SATA 6Gbps and hot-swap
- Supports SAS 12Gbps (single channel) & SATA 6Gbps and hot-swap
- Supports MiniSAS HD and SATA power cables with locking latch design
- Industry leading 3 year warranty with exceptional customer support

Model Number	MB998IP-B
Color	Black
Host Interface	2 x miniSAS HD 8643
Drive Fit	8 x 2.5" SAS / SATA SSD or HDD (5mm - 7mm thickness)
Drive Bay	Single 5.25" half height device bay
Transfer rate	SATA Up to 6 Gb/sec SAS up to 12Gbps (Single channel)
Insert & Extract connection Via Structure	Direct SATA/SAS hard drive connection Metal
Device Power	2 x 15pin SATA power port
Drive Cooling	Dual 40mm rear cooling fan with controller Metal heat dispersion
Power Indicator	Solid green LED
HDD Access Indicator	Flashing green LED
Dimension (L x W x H)	172 x 146 x 41.3mm
Weight	1.93 lbs