

TELEPHONE

TELEPHONE CORD

Telephone Cords

Modular Handset Coil Cords RJ-22 (4P4C)

	6'		12'		25'			Color	AWG	Conductor
			30-9526		30-9536			Ash	26	4
			30-9524		30-9531			Beige	26	4
					30-9531-BU			Beige	26	4
			30-9519		30-9529			Black	26	4
					30-9529-BU			Black	26	4
			30-9524		30-9534			Brown	26	4
			30-9541		30-9551			Gray	26	4
			30-9528		30-9538			Ivory	26	4
					30-9538-BU			Ivory	26	4
	30-9565		30-9525		30-9535			Light Almond	26	4
					30-9535-BU			Light Almond	26	4
			30-9520		30-9530			White	26	4
					30-9530-BU			White	26	4
					30-9539			Blue		4



Extension Cords (Modular Plug to Plug) 6P4C, 6P6C and 8P8C

5.25"	2'	7'		15'	25'	50'	100'	Color	AWG	Conductor
					30-9509			Light Almond	26	4
	30-9572	30-9579		30-9502	30-9503 -BU		30-9553	White		
					30-9507			Black	26	4
		30-9559		30-9513	30-9514	30-9549	30-9548	Ivory	26	4
				30-9513-BU	30-9514-BU			Ivory	26	4
					30-9577			White	26	6
30-9546		30-9569		30-9515	30-9516			Silver	26	4
		30-9569-BU		30-9515-BU	30-9516-BU			Silver	26	4
		30-9575		30-9566	30-9576			Silver	26	6
				30-9568	30-9578			Silver	26	8



Modular Telephone Replacement Cords (Spade Lugs to Modular Plug) 6P4C

	6'				25'			Color	AWG	Conductor
	30-9544							Ivory	26	4
								Ivory	26	4
	30-9540				30-9542			Silver	26	4
	30-9540-BU							Silver	26	4



Extension Cords (Plug to Single Modular Jack) 6P4C

25'			Color	AWG	Conductor
30-9506			Ivory	26	4
30-9506-BU			Ivory	26	4
30-9586			White	26	4



Extension Cords (Plug to Twin Modular Jack) 6P4C

25'			Color	AWG	Conductor
30-9508			Ivory	26	4



ADAPTERS/COUPLERS



Fig. 1



Fig. 3



Fig. 5



Fig. 7



Fig. 9




Fig. 2



Fig. 4



Fig. 6



Fig. 8

Modular Adapters

Retail Part No.	Bulk Part No.	Figure Number	Male Contact	# Female Jacks	# Female Contacts per Jack	Color	Function
30-9654	30-9654-BU	1	4	2	4	Ivory	Splits a 4 conductor jack into 2, 4 conductor jacks
30-9615	30-9615-BU	1	4	2	4	White	Splits a 4 conductor jack into 2, 4 conductor jacks
30-9647	30-9647-BU	1	6	2	6	Ivory	Splits a 6 conductor jack into 2, 6 conductor jacks
30-9646	30-9646-BU	1	6	2	6	White	Splits a 6 conductor jack into 2, 6 conductor jacks
30-9649	30-9649-BU	2	8	2	8	Ivory	Splits an 8 conductor jack into 2, 8 conductor jacks
30-9648	30-9648-BU	2	8	2	8	White	Splits an 8 conductor jack into 2, 8 conductor jacks
30-9655	-	3	4	2	2x2	Ivory	Converts a 2-line jack into 2 single jacks
30-9656	30-9656-BU	4	4	3	4	Ivory	Splits a 4 conductor jack into 3, 4 conductor jacks
30-9617	30-9617-BU	4	4	3	4	White	Splits a 4 conductor jack into 3, 4 conductor jacks
30-9658	-	5	4	3	1x4, 2x2	Ivory	Converts a 2-line jack into 1-2 combo, and 2 single jacks
30-9663	-	4	6	3	2	Ivory	Splits a 6 conductor jack into 3, 2 conductor jacks
30-9664	-	4	6	3	2	White	Splits a 6 conductor jack into 3, 2 conductor jacks

Modular In-line Couplers

Retail Part No.	Bulk Part No.	Figure Number	# Female Jacks	# Female Contacts per JACKS	Color	Function
30-9678	30-9678-BU	6	2	4	Ivory	Reverse - Voice Communications
30-9618	30-9618-BU	6	2	4	White	Reverse - Voice Communications
30-9686	30-9686-BU	6	2	6	Ivory	Reverse - Voice Communications
30-9682	30-9682-BU	6	2	6	Ivory	Straight through - Data Communications
30-9687	30-9687-BU	6	2	6	White	Reverse - Voice Communications
30-9683	30-9683-BU	6	2	6	White	Straight through - Data Communications
30-9688	30-9688-BU	6	2	8	Ivory	Reverse - Voice Communications
30-9684	30-9684-BU	6	2	8	Ivory	Straight through - Data Communications
30-9689	30-9689-BU	6	2	8	White	Reverse - Voice Communications
30-9685	30-9685-BU	6	2	8	White	Straight through - Data Communications

Modular 3-Way Couplers

Retail Part No.	Figure Number	# Female JACKS	# Female Contacts per Jack	Color	Function
30-9679	7	3	4	Ivory	Creates 2 modular jack outlet for the end of a modular extension cord
30-9669	7	3	4	White	Creates 2 modular jack outlet for the end of a modular extension cord

Retrofit Adapters

Retail Part No.	Bulk Part No.	Figure Number	Male Contact	# Female JACKS	# Female Contacts per Jack	Color	Function
30-9601	30-9601-BU	8	Screw Term	1	4	White	Converts hardwired system to modular, w/ cover
30-9650	30-9650-BU	9	4 Prong	1	4	Ivory	Converts standard 4 prong to modular

ACCESSORIES



Fig. 4



Fig. 1



Fig. 2



Fig. 3

Retail Part No.	Bulk Part No.	Figure Number	Description	Features
30-6000		1	Standard Telephone Pick-up	For Recording or Amplifying Both Sides of a Conversation
30-9314		2	The Tangle-Tamer	Keeps Telephone Cords From Tangling
30-9310	30-9310-BU	3	Twistfree-Clear	Prevents Cords From Becoming Twisted & Tangled
30-9312		3	Twistfree-Light Almond	Prevents Cords From Becoming Twisted & Tangled
30-9313		3	Twistfree-White	Prevents Cords From Becoming Twisted & Tangled
30-9835		4	Outdoor Telephone Bell	Weather Resistant; Ideal For Factory, Farm or Garage

MULTI-LINE PRODUCTS




Fig. 6



Fig. 7



Fig. 8

Retail Part No.	Bulk Part No.	Figure Number	Description	Features
30-9800	30-9800-BU	6	Wire Junction-With Modular Plug 6"	Enables You to Add Outlets For Telephones
30-9801	30-9801-BU	6	Wire Junction Without Modular Plug	Enables You to Add Outlets For Telephones
30-9802		7	5-Outlet Modular 4 Conductor Junction Box w/Cord	Use 5 Telephone Devices From One Jack
30-9812		8	3-Line Multi-Line-to-Modular Jack Adapter	Converts Multi-Line Service 50 Pin Connector

AUDIO ENHANCEMENT PRODUCTS



Fig. 9



Fig. 10



Fig. 11



Fig. 12



Fig. 13

Retail Part No.	Bulk Part No.	Figure Number	Description	Features
30-7501		9	Telephone Amplifier	Increases Volume
30-7520		10	Telephone Extension Ringer	Use in Basement, Garage, Laundry Room, Etc. Not Adjustable/Not Outdoors
30-7521		11	Telephone Extension Ringer	Combo Light & Ringer For Remote Locations
30-7523		12	Light Flasher	Visually Signals Incoming Calls
30-7525		13	Strobe Flasher	Bright Strobe & Ringing Alert