

GUS402

2x4 USB 2.0 Peripheral Sharing Switch



The IOGEAR 2x4 USB switch is a USB 2.0 peripheral sharing switch that allows two computers to share up to four USB devices, such as a keyboard, mouse, printer, portable hard drive, etc.

The GUS402 eliminates the cost of having multiple sets of USB devices for each computer. It also cuts down the cable clutter of your work area. Switching from computer to computer is easy with the simple press of a button and an LED to indicate the selected computer. You can also charge and sync your mobile devices through this unit.


The GUS402 is USB 2.0 compliant with a data transfer rate of up to 480 Mbps and is hot swappable. It comes with over current protection to prevent your devices from being damaged by sudden current changes from the surrounding environment.

- Enables two computers to share up to 4 USB peripheral devices, more devices can be supported by adding USB hubs
- Easily switch to any of your connected computers with the press of a button
- USB 2.0 compliant, supporting data transfer rates of up to 480Mbps
- Charge mobile devices such as smart phones on any of the USB device port
- LED indicators for the port focus of the active computer
- Over-current protection
- Supports hot-plugging which allows easily add or remove computers connected to the installation without having to power down the switch
- Molded in cable design simplifies the connections
- Cable lengths: USB output cables = 3.8ft, selection button cable = 6ft



How does it work?

- Connect your USB device to 2x4 USB 2.0 Peripheral Sharing Switch
- Use 2x4 USB 2.0 Peripheral Sharing Switch cables to your computers



Requirements

- For PC Users
- Windows XP, Windows Vista, Windows 7, Windows 8/8.1, 10
 - Available USB 2.0 port
 - Chrome Book
 - Linux®, Unix and other USB supported systems*
- *Additional drivers and support may be needed

Package Contents

- 1 x 2x4 USB 2.0 Peripheral Sharing Switch
- 1 x Quick Start Guide
- 1 x Warranty Card

- For MAC Users
- Mac 8.6 or greater.
- Requires OS X for USB 2.0 support
- Available USB 2.0 port

Specifications

Function	GUS402	Dimensions	GUS402
POP Information			
		10" Peg Hook	4
		6" Peg Hook	3
Unit Dimensions			
		Height	.98" (25mm)
		Depth	3.23" (82mm)
		Length	3.03" (77mm)
Unit Package Dimensions			
		Width	6.18" (157mm)
		Height	8.77" (223mm)
		Length	2.12" (55mm)
Master Carton			
		Width	7.87" (20cm)
		Height	7.1" (18cm)
		Depth	15" (38cm)
		Master Carton Qty.	6
Weight			
		Master Carton Wt.	3.8lb (1.74kg)
Physical Properties			
		Unit Weight	.31lbs (.14kg)
		Unit Weight with package	.52lbs (.24kg)