

ESD/STATIC PROTECTION



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8



Fig. 9




Fig. 10



Fig. 11



Fig. 12

ESD/Static Protection

Retail Part No.	Figure No.	Description	Features
20-8004	1	Medium to Large Wrist Strap	10' Coil Cord, Banana Plug/Alligator Clip, 1 meg Ohm Resistance for Safety
12-8012	1	GC Professional Adjustable Wrist Strap Kit	6' Coil Cord, 4 mm Snap Stud and Alligator Clip
12-8013	1	Wrist Strap Only	for 12-8012
12-8020	1	Coil Cord Only	for 12-8012
12-8010	1	Adjustable Economy Wrist Strap Kit	6' Coil Cord, 4 mm Snap Stud and Alligator Clip
12-8011	1	Wrist Strap Only	for 12-8010
12-8018	2	Adjustable Economy Heel Grounder	2-Layer Rubber Composite Sole Material, 14.5" Conductive Ribbon
12-8055	3	Combination Wrist Strap/Footwear Tester	Indicates Low-pass or High Results
12-8056	3	Combination Tester/Adapter	for 12-8055
12-8057	3	Stand and Baseplate	for 12-8055
12-8058	3	Footplate and Cord	for 12-8055
12-8050	4	Touch Type on Demand Wrist Strap Tester	Tests the Entire Circuit
12-8051		AC Adapter	for 12-8050
12-8032	5	Common Point Ground Cords for Bench Mats	Custom Tailor Installation
12-8024	5	Ground Cords for Floormats with 10 mm Studs	10' Yellow Striped Green Ground Cord, Terminated w/#10 (.200") Ring Terminal
12-8026	5	Ground Cords for Floormats with 10 mm Studs	Custom Tailor Installation (No Workstation)
12-8028	6	2 Pack, 10 mm Snap Sockets	for 12-8026
12-8029	6	2 Pack, 3/8" Push and Clinch 10 mm Snap Stud	for 12-8026
12-8034	6	2 Pack, 10 mm Snap Socket Adapter	for Use with ESD Grounding Mats, Adapts 10 mm Socket to 10 mm Socket
12-8030	7	Dual Bench Mount	2 Person Grounding
12-8038	8	Portable Field Service Kit	Work Surface, Wrist Strap, and Grounding Cord
12-8042	9	Dissipative Workstation Kit	Blue Bench Mat and Common Point Ground Cord
12-8043	9	ESD Two Layer Workstation Mat (24" x 40')	Use in Soldering or Assembly Area
12-8044	9	Two Layer Workstation Kit (18" x 24")	Common Ground Point (12-8032)
12-8045	9	ESD Three Layer Workstation Mat (24" x 40')	Use in Soldering or Assembly Area
12-8046	9	Three Layer Workstation Kit (18" x 24")	Common Ground Point (12-8032)
12-8048	9	Floor Ground Kit (24" x 36")	Gray Floor Mat, 1 Ground Cord, 1 Snap Socket (12-8028)
12-8047	10	Anti-fatigue Dissipative Floor Mat (3' x 60')	Foamed Soft Mat
12-8047-SNKT		Universal Snap Kit	10 mm Stud, 10 mm Socket, a Long and Short Screw
12-8060	11	Touch Type Wrist Strap Tester	AC Operation, Operates on Demand, Common Point Grounding Jacks for 2 Straps
12-8061	12	Anti-static Packaging Tape	1" Width
12-8062	12	Anti-static Packaging Tape	2" Width