



48-22-9408

3/8" Drive 28pc Ratchet & Socket Set- SAE

★★★★★ (0) Write a review

Our MILWAUKEE® SAE 28 piece 3/8" drive Ratchet & Socket set is designed from the ground up, offering our users the Most Versatile Sockets that are Anti-Roll and Wrench-Ready. Its innovative FOUR FLAT™ Sides feature an anti-roll and wrench-ready design. The 90 tooth ratchet tool offers 4° of arc swing and a slim profile design, allowing you to work in tighter and more confined spaces, be it under the hood of a car or in the middle of a remodel. The ratchet and socket kit comes with a removable inner tray which is perfectly designed to be stored long-term in a steel storage chest. All of our sockets are stamped with SAE measurements on the flat side for easy-to-read visibility. It also comes with a durable carrying case for ultimate portability. The set comes with accessories included so that our users can get every job done, both in the garage and on the jobsite. Our ratchet and socket set is backed by our Lifetime Guarantee.

Close

INCLUDES:

(1) 1/2" Deep Well Socket

- (1) 1/2" Standard Socket
- (1) 1/4" Deep Well Socket
- (1) 1/4" Standard Socket
- (1) 1" Standard Socket
- (1) 11/16" Deep Well Socket
- (1) 11/16" Standard Socket
- (1) 13/16" Deep Well Socket
- (1) 13/16" Standard Socket
- (1) 15/16" Standard Socket
- (1) 3/4" Deep Well Socket
- (1) 3/4" Standard Socket
- (1) 3/8" Deep Well Socket
- (1) 3/8" Standard Socket
- (1) 3" Extension
- (1) 5/16" Deep Well Socket
- (1) 5/16" Standard Socket
- (1) 5/8" Standard Socket
- (1) 5/8" Standard Socket
- (1) 6" Extension
- (1) 7/16" Deep Well Socket
- (1) 7/16" Standard Socket
- (1) 7/8" Deep Well Socket
- (1) 7/8" Standard Socket
- (1) 9/16" Deep Well Socket
- (1) 9/16" Standard Socket
- (1) 90-Tooth Ratchet
- (1) Universal Hose Adapter

Close

Where To Buy

KEY FEATURES

SPECIFICATIONS

REVIEWS

MOST VERSATILE SOCKETS. ANTI-ROLL, WRENCH-READY.

FOUR FLAT™ Sides on socket deter rolling

FOUR FLAT™ Sides feature wrench-ready design

90 tooth design with 4 degrees of arc swing for tight work spaces

Removable inner tray specifically designed for steel storage case

Slim profile head with flush direction lever

Stamped Socket Sizes Portable Carrying Case

Lifetime Guarantee

↓ **Download Service Parts List** (<https://documents.milwaukeetool.com/54-49-9007.pdf>)

PRODUCT SPECIFICATIONS

Width	1.8"
Warranty	Lifetime Guarantee
Weight	5.76lbs
Height	15.1"
Length	9.9"

REVIEWS



Be the first to review this product