

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0334810401](#)  
**Status:** **Active**  
**Overview:** [MX150 Sealed and Unsealed Connector System](#)  
**Description:** MX150 Sealed Male Connector, Single Row, 4 Circuits, Polarization A, without Connector Position Assurance, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-33472-100-CH-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-33472-100-FR-001 (PDF)</a>
<a href="#">Product Specification PS-33471-000-001 (PDF)</a>	<a href="#">Packaging Specification PK-31300-635-001 (PDF)</a>
<a href="#">Product Specification PS-34646-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-33472-100-001 (PDF)</a>	

**General**

Product Family	Crimp Housings
Series	33481
Application	Power, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
More Detailed Tech Information	<a href="http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications">http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications</a> -Partnership
Overview	<a href="#">MX150 Sealed and Unsealed Connector System</a>
Product Name	MX150
UPC	756054457320

**Physical**

Circuits (maximum)	4
Circuits Detail	4
Color - Resin	Black, Natural
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	8.933/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C


**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-33472-100-001, AS-33472-100-CH-001, AS-33472-100-FR-001
Packaging Specification	PK-31300-635-001
Product Specification	PS-33471-000-001, PS-34646-001-001
Sales Drawing	SD-33481-041



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[33481](#) Series

**Mates With**

[33471](#) Female Single Row Sealed Connector

**Use With**

[33000](#) MX150 Male Terminal, [34345-0001](#) MX150 Cavity Plug Sealed

This document was generated on 10/23/2018

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**