

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0430200200](#)
Status: **Active**
Overview: [Micro-Fit 3.0 Connector System Product Family](#)
Description: [Micro-Fit 3.0 Plug Housing, Dual Row, 2 Circuits, UL 94V-0, Panel Mount Ears, Low-Halogen, Black](#)

Documents:

| | |
|--|--|
| Drawing (PDF) | Product Specification TS-46235-001-001 (PDF) |
| 3D Model | Packaging Specification PK-43020-001-001 (PDF) |
| Product Specification PS-43045 (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-43045-001 (PDF) | Product Literature (PDF) |
| Product Specification TS-43045-001-001 (PDF) | |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|-----------------------------|---|
| Product Family | Crimp Housings |
| Series | 43020 |
| Application | Power, Wire-to-Wire |
| Overview | Micro-Fit 3.0 Connector System Product Family |
| Product Literature Order No | 987650-5984 |
| Product Name | Micro-Fit 3.0 |
| UPC | 800754383264 |

Physical

| | |
|-------------------------------|----------------|
| Circuits (maximum) | 2 |
| Color - Resin | Black |
| Flammability | 94V-0 |
| Gender | Plug |
| Glow-Wire Capable | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 0.456/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Panel Mount | Yes |
| Pitch - Mating Interface | 3.00mm |
| Pitch - Termination Interface | 3.00mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |

Solder Process Data

| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|--|
| Packaging Specification | PK-43020-001-001 |
| Product Specification | PS-43045, PS-43045-001, TS-43045-001-001, TS-46235-001-001 |
| Sales Drawing | SDA-43020-**** |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[43020 Series](#)

Mates With

Micro-Fit 3.0 Receptacle Housings [43025](#)

Micro-Fit 3.0 Cable Assembly [245132](#)

Use With

Micro-Fit 3.0 Male Crimp Terminals [43031](#)

This document was generated on 10/24/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION