

GFR281W6

## 56-in-1 Memory Card Reader/Writer



IOGEAR's newest Universal Memory Bank, 56-in-1 Memory Card Reader/Writer, is an ideal solution for hi-speed, bi-directional image and data file transfer between your computer and multimedia devices. Images and data can be downloaded directly from your memory cards without using additional adapters\*. It works with all major memory card formats and supports high capacity: CompactFlash/Micro Drive, SD/SDHC/Mini SD/MMC, Olympus and Fuji Film flash memory, T-Flash/microSD/ microSDHC, Memory Stick/MS Duo, Memory Stick Micro (M2). With direct USB 2.0 high-speed file transfer (up to 480Mbps) from memory cards used in your digital cameras, cellphone, or MP3 devices, you can save time and conserve power on devices. It also instantly transfers your slotMusic™ songs to your PC or Mac. No matter where you go, IOGEAR's Universal Memory Bank helps you to easily bring your digital images and data with you.

Supporting Media List: - Compact Flash/Micro Drive: CF-Type I, CF-Type II, CF-Ultra II, Micro Drive, CF-Pro II, CF-Extreme, CF-Extreme III, CF-PSP II, CF-Supper, CF-Ultra X - SD/SDHC: SD, SDHC, SD-Pro, SD-Pleomax, SD-Pro C, SD-Ultra II, SD-Ultra II Plus, SD-Extreme III, SD-Ultra X, SD-Turbo, SD-Supper, SD Max, Mini SD, Mini SD-Pro, Mini SD-Pleomax, MMC, MMC-Pleomax, MMC Pro, HS-MMC, MMC Plus, MMC-Plus Turbo, RS MMC, RS MMC-Pleomax, RS MMC-Speed, RS MMC-Max, MMC Mobile, MMC Mobile-ProC, MMC Mobile-Pocketnet, MMC Micro\* - Olympus DC Card: Olympus DC Card, Olympus DC Card(M), Olympus DC Card (H) - microSD/microSDHC: microSD/microSDHC, T-Flash - Memory Stick: MS, MS-Magic Gate, MS-PRO Magic Gate, HS-MS-PRO Magic Gate, MS-DUO, MS DUO Magic Gate, MS-PRO Duo, HS-MS-PRO Duo, HS-MS-PRO Duo Magic Gate, MS-PRO Duo-PSP, MS-PRO Duo-Gaming Memory Stick - M2: Memory Stick Micro (M2)

- Easy installation; Plug-n-Play
- Reads and writes multiple media cards at one time
- **CompactFlash Type I, II**
- **High Capacity support: SDXC/SDHC/microSDHC**
- **SD/Mini SD/MMC/microSD/T-Flash**, transfer your **slotMusic™** songs to your PC or Mac
- **Olympus and Fuji Film flash memory**
- **Memory Stick/MS Duo**
- **Memory Stick Micro (M2)**
- Remarkable high-speed digital image and data transfer to computer
- USB 2.0 transfer speeds up to 480Mbps.
- No power adapter needed
- Works with all popular memory cards without additional adapters required
- Specifically designed for digital cameras and also ideal for using with Palmtop PCs, Handheld PCs, PDAs, Voice Recorders and other mobile electronics
- Hot swapping capacity for replacing PC storage cards without restarting the computer

**Drive letter recognition software can be downloaded from "Driver & Manual" section. The software can replace confusing icons with memory card slot icons for easier access.**



**Requirements**

- **For PC users:**
  - Windows® 2000, XP, Vista, 7, 8/8.1
  - Available USB port (USB 2.0 port for Hi-Speed mode)
  -
- **For MAC users:**
  - Mac OS 10.1.2 or greater
  - Available USB port (USB 2.0 port for Hi-Speed mode)

**Package Contents**

- 1 x 56-in-1 Card Reader/Writer
- 1 x USB Cable (Type A - mini B)
- 1 x Quick Start Guide

**Specifications**

Function	GFR281W6	Dimensions	GFR281W6
<b>Housing</b>		<b>POP Information</b>	
Case	Plastic	10" Peg Hook	5
Ports	(1) USB mini-B port	6" Peg Hook	3
Operating Temperature	- 40 ~ + 176 ° F ( - 40 ~ + 80 ° C)	<b>Unit Dimensions</b>	
Storage Temperature	+ 32 ~ + 158 ° F ( 0 ~ + 70 ° C)	Height	0.625 in.
Operating System Support	Win 2000, XP, Vista, MAC 10.11+	Depth	2.3 in.
USB Specification	USB 1.1 and 2.0 compliant	Length	4 in.
Transfer Rate	480 Mbps	<b>Inner Pack</b>	
Humidity	20-80% RH, (Non Condensing)	Width	6.75 in.
Cable Type	1 - USB 2.0 Cable (Type mini-B to A) 3-feet	Height	7.5 in.
Power Mode	Bus Powered	Length	10 in.
		Inner Pack Qty.	6
		<b>Unit Package Dimensions</b>	
		Width	6.75 in.
		Height	10 in.
		Depth	2.25 in.
		<b>Master Carton</b>	
		Width	10 in.
		Height	14 in.
		Depth	15.5 in.
		Master Carton Qty.	24
		<b>Weight</b>	
		Master Carton Wt.	11 lb.
		Inner Pack Wt.	2.6 lb.
		Unit Pack Wt.	0.5 lb.
		Unit Wt.	0.25 lb.