

# PYLE®

[www.PyleAudio.com](http://www.PyleAudio.com)



## ***PDVRCAM11***

### **Compact HD Dash Cam**


# USER MANUAL

**Connection:**

The DVR is supplied power by cigarette-lighter USB power cable, there is no need to connect to extra DC cable. Simply mount the camera in a convenient location and connect the power cable to the USB input located on the side of the screen display unit.

**Installation:**

The DVR system includes a suction cup that mounts conveniently to your windshield.



#### Function:

1. Long press the power button, the DVR will power off. Short press the power button, the DVR will enter the MENU interface. The MENU is with Video and Setup two functions.
2. The Video is include "Resolution", "Loop Recording", "Motion Detection", "Date Stamp", "Record Audio", "GSENSOR".
3. The Setup is include "Date/Time", "Auto power off", "Beep Sound", "Language", "Frequency", "TV Mode", "Default Setting", "Version".
4. The "▲" "OK" "▼" button serve as setting, you can press them to choose access setting.
5. The DVR is with "Micro SD" connector, you can insert the SD card for recording.
6. The "HDMI" connector for connecting to computer, MP5 etc..
7. The "USB" connector for connecting to cigarette-lighter.

## Interface & Options

Resolution:	You can choose the video's quality between 1080FHD(1920X1080pixels)and QVGA(320X240pixels)
Loop Recording:	You can choose times:3min/5min/10min.If you are not need this function, you can choose"off".
Motion Detection:	This function is acquiesced in "off". If there have movement in front of the car, the DVR will record video automatically once you set as "on".
Date Stamp:	It can be set as"off" or "on".
Record Audio:	If you set as"on", the DVR will record the sounds.
GSENSOR:	This function is very important, it will lock the video if the car has a crash or the speed of the car is too fast, it can provide the evidence.
Date/Time:	You can set the date and time.
Auto Power Off:	There are 4 choice to this function:"off"、"2min"、"5min"and "10min".If you choose the times, the DVR will auto power off when it is in standby mode. We suggest you set as"off".
Beep Sound:	You can set as"off" or "on" that depends on your needs.
Language:	The language acquiesced in "English", you also can choose Chinese、ITA、ESP、PORT、DEUT、FRAN etc..
Frequency:	You can set as"50Hz"or "60Hz".
TV Mode:	You can set as"PAL" or "NTSC".
Default Setting:	You can restore default setting which all the machine will come back to factory setting.
Version:	You can find the version of software.

## PDVRCAM11 - Dash Cam

<b>Features:</b> HD 1080p Video Recording Button-Activated Image Capture 1.5" Digital LCD Display Micro SD Memory Card Slot Night Vision Low Light Illumination Built-in Microphone for Audio Recording Auto Record & Loop Recording Function Tilt Angle & Rotation Adjustable Extra Compact & Unobtrusive Design Universal Windshield / Dashboard Mountable Built-in Rechargeable Battery G-Sensor Impact Video File Auto-Saving Simple Button Control Operation Includes USB Vehicle Cigarette Lighter Power Accessory Cable Easy File Saving & Sharing Works with Windows & Mac	<b>Technical Specs:</b> Selectable Video Resolution: 1080p, 720p, 480p Selectable Image Resolution: 10MP, 8MP, 5MP, 4MP, 3MP File Format: Video (AVI), Image (JPEG) Imaging Sensor: 5.0 CMOS MP AV Interface: AV-Out Lens: f2.0 Six-Glass, 130 Degree Wide-Angle Screen Resolution: 280 x 120 Pixels Video System: PAL/NTSC Compatible Time Stamp: ON/OFF Maximum Micro SD Card Support: 32GB Power: DC 5V Camera Dimensions (L x W x H): 2.7" x 1.5" x 1.6"
--	--