



Part of Ant Group Ltd

## IC Workstation and Mat Cleaner

### Details:

#### IC Workstation and Mat Cleaner

##### SARA Hazardous Category

This product has been reviewed according to the EPA hazard categories under Section 311 & 312 of the Superfund Amendment and Reorganization Act of 1986 and is considered under applicable definitions to meet the following category: Not to have met any hazardous category.

##### TOXIC Substance Control Act (TSCA)

All ingredients are on the TSCA inventory or are not required to be listed on the TSCA inventory.

Hazardous Components: OSHA PEL ACGIH TIV



### Notes:

Physical / Chemical Characteristics:	
Boiling Point	101 degrees C
Vapor Pressure (mm Hg)	n/a
Vapor Density (AIR=1)	Not established
Specific Gravity (H2O =1)	1.0
Melting Point	n/a
Evaporation Rate (Butyl Actetate =1)	0.71
Solubility in Water	100%
Appearance and Odor	Clear Blue Liquid with Mild Odor

Fire and Explosion Hazard Data:	
Flash Point (Method Used) Flammable Limits	n/a
Extinguishing Media	CO2
Special Fire Fighting Procedures	Precaution - Use Breathing Apparatus
Unusual Fire and Explosion Hazards	none

Reactivity Data:	
Stability Unstable	Stable X
Conditions to Avoid	Evaporation - open containers may change concentrations
Incompatibility (Materials to Avoid)	n/a
Hazardous Polmerization May Occur	Conditions to avoid X Will not occur X



Part of Ant Group Ltd

## IC Workstation and Mat Cleaner

Health Hazard Data:	
Routes of Entry	Inhalation - n/a Skin - X Ingestion - n/a
Health Hazards (Acute and Chronic)	Prolonged contact will remove body oils
Carcinogenic	n/a
Signs and Symptoms of Exposure	Dry flaking skin
Medical Conditions Aggravated by Exposure	n/a
Emergency and First Aid Procedures	Replenish body oils with body lotion

Precaution for Safe Handling and Use:	
Steps to be taken if released or spilt	Mop up spills or rinse down sewer
Waste Disposal Method	Sewer
Precautions to be taken in handling and storage	Avoid temperatures >100F
Other Precautions	none

Control Measures:	
Respiratory Protection	n/a
Ventilation	n/a
Local Exhaust	n/a
Special	n/a
Protective Gloves	For long periods of exposure
Eye Protection	Goggles when splashing may occur
Other protective clothing or equipment	n/a
Work / Hygenic Practices	Normal

NFPA Rating:			
Health	Flammability	Reactivity	Personal Protection
1	0	0	1

Product Code:	Description:	Size:	Additional Notes:
106-0011	IC Workstation Mat Cleaner	32oz Spray	Each
106-0016	IC Workstation Mat Cleaner	16oz Spray	Each
106-0021	IC Workstation Mat Cleaner	1 Gallon Bottle	Each