

Compact wet and dry vacuum cleaners with filter cleaning and ergonomic design

The AERO 26 is a reliable and compact vacuum developed with a high focus on the variety of applications and end-user needs within industry, automotive and building and construction. It is a lightweight and robust machine with ergonomic design, semi-automatic filter cleaning and convenient storage solutions. A Power socket with AutoOnOff activates the machine when the power tool operates providing efficient dust extraction from the power tool.

The AERO 26 is a light-weight machine for workers within industry, automotive and building & construction featuring semi-automatic filter cleaning, ergonomic design and convenient storage. Being compact, lightweight and robust, it can easily be transported to any location. After finishing your job, the container can easily be emptied - either by dispose the standard fleece filter bag or by tipping the container by the lifting handle found on some models. The Push&Clean filter cleaning system prevents loss of performance and increase productivity during your cleaning task. Storage is made easy with several positions for suction hose, nozzles and power cord, and the built-in 2-points tube parking makes operation easy and flexible. The Aero 26 equipped with a power take off socket for use with power tools.



Picture shown may not represent model quoted

- Washable PET fleece filter with minimum 99,9% filtration efficiency
- MultiFit accessory system for ultimate flexibility
- Convenient accessory/cable storage and tool deposit
- Exhaust air blow function
- Flexible rubber strap for hose storage

• Standard equipment

Included accessories		Ref. no.	Min. required	AERO 26-21 PC 110V/50-60HZ GB	AERO 26-21 PC 230V/50-60HZ GB
<b>Filter</b>					
	Filterelement ATTIX	302000490	1	•	•
<b>System 36 Hose Vacuum Cleaner</b>					
	SUCTION HOSE D32x1800 CPL.	107405600	1		
	SUCTION HOSE D32X3500 CPL.	107406115	1	•	•
	UNIV HOSE WITH HAND TUBE D32X3500 CPL.	107409976	1		
<b>System 36 Tube</b>					



Compact wet and dry vacuum cleaners with filter cleaning and ergonomic design

Included accessories		Ref. no.	Min. required	AERO 26-21 PC 110V/50-60HZ GB	AERO 26-21 PC 230V/50-60HZ GB
	EXTENSION TUBE D36 2X505MM ST/CR	302000529	1	•	•
	TELESCOPIC TUBE D36 575-930MM CR-ST	107402654	1		
	TOOL ADAPTER WITH SUCTION REGULATION D32	107409977	1	•	•
<b>System 36 Brush/Universal Nozzle</b>					
	BRUSH NOZZLE Ø36X230 PP/PA	6086	1		
	SUCTION BRUSH D36 BLACK	302002509	1	•	•
	UNIVERSAL NOZZLE D36X115	14295	1	•	•
<b>System 36 Vac Floor Nozzle</b>					
	COMBI NOZZLE Ø36X260MM	302002365	1		
	FLOOR NOZZLE D36x300MM W/D KIT	107402706	1	•	•
<b>System 36 Crevice/Cone Nozzle</b>					
	CREVICE NOZZLE D36X200	29541	1	•	•
<b>Other</b>					
	TOOL BOX. AERO 26/31	107409980	1		

Model	AERO 26-21 PC 110V/50-60HZ GB	AERO 26-21 PC 230V/50-60HZ GB
Ref. no.	107406613	107406614

PRODUCT FEATURES

Cable holder	•	•
Softstart		
Motor speed control		



Compact wet and dry vacuum cleaners with filter cleaning and ergonomic design

Model	AERO 26-21 PC 110V/50-60HZ GB	AERO 26-21 PC 230V/50-60HZ GB
Ref. no.	107406613	107406614

PRODUCT FEATURES

Automatic on/off - electric tools	•	•
Storage of accessories	•	•
Cable rewind		
Blow function	•	•
Extra socket for tool	•	•
L-class hazardous dust approval		
Fleece filter bag 1 pcs.	•	•
Container lift/tilt handle	•	•

Technical specifications	AERO 26-21 PC 110V/50-60HZ GB	AERO 26-21 PC 230V/50-60HZ GB
Power Pmax (W)	1250	1250
Power Piec (W)	1000	1000
Mains connection (V/~/Hz/A)	110/1/50-60/16	230/1/50-60/15
Airflow rate (l/min.)	3600	3600
Vacuum (mbar/kPa)	210/21	210/21
Working sound level (dB(A))	64	64
EI cable (m)	7.5	5
Container volume (l-max)	25	25
Filter cleaning system	Push&Clean	Push&Clean
Main filter type	PET	PET
Length x width x height (mm)	375x390x530	375x390x530
Weight (kg)	9	9

• Standard equipment, ○ Supplementary accessories, □ Mountable equipment

Accessories		Ref. no.	Min. required	AERO 26-21 PC 110V/50-60HZ GB	AERO 26-21 PC 230V/50-60HZ GB
<b>System 36 Hose Vacuum Cleaner</b>					
	SUCTION HOSE D32x1800 CPL.	107405600	1	○	○
	SUCTION HOSE D32X2500 CPL.	107405599	1	○	○



## Compact wet and dry vacuum cleaners with filter cleaning and ergonomic design

Accessories		Ref. no.	Min. required	AERO 26-21 PC 110V/50-60HZ GB	AERO 26-21 PC 230V/50-60HZ GB
	SUCTION HOSE D32X3500 CPL.	107406115	1	•	•
	SUCTION HOSE D32X5000 CPL.	107402198	1	○	○
	SUCTION HOSE Ø36X3500 HEAT/OIL-RESISTANT	302001677	1	○	○
	UNI. HOSE Ø36X3000MM EVA	15805	1	○	○
	UNI. HOSE Ø36X3000MM W COUPLING EVA	46948	1	○	○
	UNI. HOSE Ø36X4000MM EVA	25537	1	○	○
	UNIV HOSE WITH HAND TUBE D32X3500 CPL.	107409976	1	○	○
<b>System 36 Tube</b>					
	ADAPTER TUBE STRAIGHT AS Ø36MM	29457	1	○	○
	CURVED HAND TUBE D36MM ST/CR	302000528	1	○	○
	CURVED HAND TUBE Ø36MM SS	46691	1	○	○
	EXTENSION TUBE D36 2X500MM ALU	107400032	1	○	○
	EXTENSION TUBE D36 2X505MM ST/CR	302000529	1	•	•
	EXTENSION TUBE D36 2X515MM PLASTIC	40696	1	○	○



## Compact wet and dry vacuum cleaners with filter cleaning and ergonomic design

Accessories		Ref. no.	Min. required	AERO 26-21 PC 110V/50-60HZ GB	AERO 26-21 PC 230V/50-60HZ GB
	EXTENSION TUBE D36 3X350 MM SS	107416995	0	○	○
	EXTENSION TUBE Ø36 2X505MM SS	107408074	1	○	○
	TELESCOPIC TUBE D36 575-930MM CR-ST	107402654	1	○	○
	TELESCOPIC TUBE Ø36X550-970 SS	47109	1	○	○
	TOOL ADAPTER D27 QUICKSYSTEM	302000535	1	○	○
	TOOL ADAPTER WITH SUCTION REGULATION D32	107409977	1	●	●
<b>Filter Bag</b>					
	FILTER BAG AERO 4 PCS	302002404	1	○	○
<b>Filter</b>					
	FILTER ELEMENT Ø185X140 HEPA H14	302001095	1	○	○
	Filterelement ATTIX	302000490	1	●	●
<b>System 36 Vac Floor Nozzle</b>					
	COMBI NOZZLE Ø36X260MM	302002365	1	○	○
	COMBI NOZZLE Ø36X260MM PP	302000477	1	○	○
	ELECTRIC TURBINE BRUSH Ø36X305MM 230V	11664	1		
	FLOOR NOZZLE COMBI Ø36X270MM	107417892	0	○	○
	FLOOR NOZZLE D36x300MM W/D KIT	107402706	1	●	●
	FLOOR NOZZLE D36X400MM W/D	302003666	1	○	○

## Compact wet and dry vacuum cleaners with filter cleaning and ergonomic design

Accessories		Ref. no.	Min. required	AERO 26-21 PC 110V/50-60HZ GB	AERO 26-21 PC 230V/50-60HZ GB
	FLOOR NOZZLE Ø36X300MM	302002331	1	○	○
	FLOOR NOZZLE Ø36X330 ALU	5147	1	○	○
	FLOOR NOZZLE Ø36X360MM WET/DRY	60356	1	○	○
	FLOOR NOZZLE Ø36X400 SPECIAL WET/DRY	5149	1	○	○
	NOZZLE ALU. 450XØ36MM DRY	15348	1	○	○
	NOZZLE ALU. 450XØ36MM WET	15349	1	○	○
	TURBINE BRUSH NOZZLE 300XØ36MM	54118	1	○	○
	WATER SUCTION NOZZLE Ø36X300	7270	1	○	○
<b>System 36 Brush/Universal Nozzle</b>					
	BRUSH NOZZLE Ø36X70	5146	1	○	○
	BRUSH NOZZLE Ø36X230 PP/PA	6086	1	○	○
	OVAL BRUSH NOZZLE Ø36MM	40455	1	○	○
	RADIATOR BRUSH NOZZLE Ø36X420	5144	1	○	○
	SUCTION BRUSH D36 BLACK	302002509	1	●	●

## Compact wet and dry vacuum cleaners with filter cleaning and ergonomic design

Accessories		Ref. no.	Min. required	AERO 26-21 PC 110V/50-60HZ GB	AERO 26-21 PC 230V/50-60HZ GB
	TURBINE HAND BRUSH NOZZLE Ø36X150MM	41275	1	○	○
	UNIV NOZZLE Ø36X150 ALU	5145	1	○	○
	UNIVERSAL NOZZLE D36X115	14295	1	●	●
<b>System 36 Crevice/Cone Nozzle</b>					
	CREVICE NOZZLE D36X200	29541	1	●	●
	CREVICE NOZZLE Ø36X300 PP	6084	1	○	○
	CREVICE NOZZLE Ø 36X15X920 ST/CR	17836	1	○	○
	DIA. TUBE NOZZLE Ø36x190 MM GREY RUBBER	5067	1	○	○
	FLAT NOZZLE Ø36MM RUBBER	40456	1	○	○
<b>Other</b>					
	SPARK EXTINGUISHER Ø50	34591	1	○	○
	TELESCOPIC TUBE HOLDER KIT D32	107409978	1	○	○
	TOOL BOX. AERO 26/31	107409980	1	○	○
	TUBE HOLDER KIT D36	107409979	1	○	○
<b>System 50 Tube</b>					
	ELBOW 90 Ø 50MM	5089	1	○	○
<b>System 27 Brush/Universal Nozzle</b>					
	BRUSH CURRY COMB Ø 27MM	6093	1	○	○

## Compact wet and dry vacuum cleaners with filter cleaning and ergonomic design

Accessories		Ref. no.	Min. required	AERO 26-21 PC 110V/50-60HZ GB	AERO 26-21 PC 230V/50-60HZ GB
	CURRY COMB Ø27MM	6092	1	○	○
	SPIKED CURRY COMB Ø 27MM	6094	1	○	○
<b>Vacuum Accessory Set</b>					
	ANIMAL CARE SET Ø27MM 4-PCS	6095	1	○	○
	BOILER SET Ø 36MM 4-PCS	60430	1	○	○
	CAR SET Ø36MM 3 PCS	63211	1	○	○
	HOME & OFFICE SET Ø36MM 5-PCS	63212	1	○	○
	HOSE SET Ø36MM 3 PCS	63210	1	○	○
	INDUSTR. FLOOR SET Ø36MM 4-PCS	63214	1	○	○
	TRADE AND IND. SET Ø36MM 5-PCS	63213	1	○	○
	WATER VACUUM SET Ø36MM 3- PCS	7727	1	○	○
	WORKSHOP HOSE KIT SYSTEM 36 5-PCS	107413545	0	○	○

## Compact wet and dry vacuum cleaners with filter cleaning and ergonomic design

Accessories		Ref. no.	Min. required	AERO 26-21 PC 110V/50-60HZ GB	AERO 26-21 PC 230V/50-60HZ GB
	WORKSHOP KIT BASIC D36MM 4PCS	107401367	1	○	○
	WORKSHOP SET Ø36MM 6-PCS	302000927	1	○	○
<b>Special Filter</b>					
	FILTER PROTECTIVE COVER Ø185X200	11801	1	○	○
	WET FILTER SIEVE Ø143X140MM SS	15475	1	○	○
<b>System 27 Hose Vacuum Cleaner</b>					
	UNIV HOSE Ø27X3500 WITH TOOL ADAPTER EVA	14289	1	○	○
<b>Disposal Bag</b>					
	DISPOSAL BAG ATTIX 3/30/40 5 PCS	302000804	1	○	○
	DISPOSAL BAG FOR FILTER ELEMENT	30082	1	○	○