

# F204 B-125/0.03-L



F204 B-125/0.03-L Residual Current Circuit Breaker

## General Information

Extended Product Type	F204 B-125/0.03-L
Product ID	2CSF204523R1950
EAN	8012542988700
Catalog Description	F204 B-125/0.03-L Residual Current Circuit Breaker
Long Description	The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications. This product is particularly suitable for the protection against smooth d.c. earth fault currents. This product is suitable for installations where neutral on the left is needed.

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030

## Popular Downloads

Data Sheet, Technical Information	9AKK107046A0424
Instructions and Manuals	Manual sheet inside the box

## Dimensions

Product Net Width	0.072 m
Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.500 kg

## Technical

Standards	IEC/EN 61008
Operating Characteristic	Instantaneous
Type of Residual Current	B type
Rated Residual Current	30 mA
Rated Current ( $I_n$ )	125 A
Number of Poles	4
Position of Neutral Terminals	Left
Power Loss	at Rated Operating Conditions per Pole 7.5 W

---

## Environmental

Ambient Air Temperature	Operation -25 ... +40 °C Storage -40 ... +70 °C
RoHS Status	Following EU Directive 2011/65/EU

---

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5602
Environmental Information	Refer to RoHS
Instructions and Manuals	Manual sheet inside the box
RoHS Information	2CSC423001K2702

---

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.073 m
Package Level 1 Height	0.078 m
Package Level 1 Depth / Length	0.09 m
Package Level 1 Gross Weight	0.525 kg
Package Level 1 EAN	8012542988717

---

## Classifications

Object Classification Code	Q
E-nummer	2160009
ETIM 4	EC000003 - Residual current circuit breaker (RCCB)
ETIM 5	EC000003 - Residual current circuit breaker (RCCB)
ETIM 6	EC000003 - Residual current circuit breaker (RCCB)
ETIM 7	EC000003 - Residual current circuit breaker (RCCB)

---

## Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCCBs → Residual Current Devices RCCBs

