

Copper Cables

Belkin offers CAT5e and CAT6 copper cabling and connectivity products that feature quality components and utilize advanced manufacturing techniques to ensure consistent, top-quality network performance. All Belkin cables are certified to meet or exceed industry-cabling standards and come with a lifetime guarantee.

Why CAT6?

- Maximizes your network speed with higher bandwidth—perfect for VoIP, video, and file transfers
- Protects your network investment for future expansion

Belkin Cables:

- Compliant to industry standards – ETL-verified to TIA/EIA 568B and ISO/IEC 11801-compliant (CAT5e) and TIA/EIA 568B.2.1 (CAT6)
- Performance tested – tested to exceed: 100MHz for CAT5e, 500MHz for CAT6
- Molded, snagless connectors
- Stranded, 24AWG, copper conductors
- Gold-plated connector contacts

CAT6 Patch Cables

CAT6 Snagless Patch Cables							
Feet	Black	Blue	Green	Red	White	Yellow	Gray
3	A3L980b03-BLK-S	A3L980b03-BLU-S	A3L980-03-GRN-S	A3L980-03-RED-S	A3L980-03-WHT-S	A3L980-03-YLW-S	A3L980b03-S
5	A3L980-05-BLK-S	A3L980-05-BLU-S	A3L980-05-GRN-S	A3L980-05-RED-S	A3L980-05-WHT-S	A3L980-05-YLW-S	A3L980-05-S
7	A3L980b07-BLK-S	A3L980b07-BLU-S	A3L980b07-GRN-S	A3L980b07-RED-S	A3L980-07-WHT-S	A3L980-07-YLW-S	A3L980b07-S
10	A3L980-10-BLK-S	A3L980-10-BLU-S	A3L980-10-GRN-S	A3L980-10-RED-S	A3L980-10-WHT-S	A3L980-10-YLW-S	A3L980-10-S
14	A3L980b14-BLK-S	A3L980b14-BLU-S	A3L980-14-GRN-S	A3L980b14-RED-S	A3L980-14-WHT-S	A3L980-14-YLW-S	A3L980b14-S
20	A3L980-20-BLK-S	A3L980-20-BLU-S	A3L980-20-GRN-S	A3L980-20-RED-S	A3L980-20-WHT-S	A3L980-20-YLW-S	A3L980-20-S
25	A3L980b25-BLK-S	A3L980b25-BLU-S	A3L980-25-GRN-S	A3L980b25-RED-S	A3L980-25-WHT-S	A3L980-25-YLW-S	A3L980b25-S
50	A3L980b50-BLK-S	A3L980b50-BLU-S	A3L980-50-GRN-S	A3L980-50-RED-S	A3L980-50-WHT-S	A3L980-50-YLW-S	A3L980b50-S

CAT5e Patch Cables—connect your IT hardware to the network and offer reliable, practical, Gigabit-Ethernet performance.

CAT5e Snagless Patch Cables							
Feet	Black	Blue	Green	Red	White	Yellow	Gray
3	A3L791-03-BLK-S	A3L791-03-BLU-S	A3L791-03-GRN-S	A3L791-03-RED-S	A3L791-03-WHT-S	A3L791-03-YLW-S	A3L791-03-S
5	A3L791-05-BLK-S	A3L791-05-BLU-S	A3L791-05-GRN-S	A3L791-05-RED-S	A3L791-05-WHT-S	A3L791-05-YLW-S	A3L791-05-S
7	A3L791b07-BLK-S	A3L791b07-BLU-S	A3L791b07-GRN-S	A3L791b07-RED-S	A3L791-07-WHT-S	A3L791b07-YLW-S	A3L791b07-S
10	A3L791-10-BLK-S	A3L791-10-BLU-S	A3L791-10-GRN-S	A3L791-10-RED-S	A3L791-10-WHT-S	A3L791-10-YLW-S	A3L791b10-S
14	A3L791b14-BLK-S	A3L791b14-BLU-S	A3L791b14-GRN-S	A3L791b14-RED-S	A3L791-14-WHT-S	A3L791b14-YLW-S	A3L791b14-S
20	A3L791-20-BLK-S	A3L791-20-BLU-S	A3L791-20-GRN-S	A3L791-20-RED-S	A3L791-20-WHT-S	A3L791-20-YLW-S	A3L791-20-S
25	A3L791b25-BLK-S	A3L791b25-BLU-S	A3L791b25-GRN-S	A3L791b25-RED-S	A3L791b25-WHT-S	A3L791b25-YLW-S	A3L791b25-S
50	A3L791b50-BLK-S	A3L791b50-BLU-S	A3L791b50-GRN-S	A3L791b50-RED-S	A3L791b50-WHT-S	A3L791b50-YLW-S	A3L791b50-S

For more information, contact your local dedicated Insight team at Belkin (800) 223-5546 ext. 2360 or _belkorderstatus@belkin.com.