ROLINE HQ VGA Cable + Ferrite + DDC, HD15, M/M, 15.0 m

Product No.	11.04.5665
Manufacturer	ROLINE
Manufacturer No.	11.04.5665
EAN (single piece)	7611990125494



- High quality cable for connection of a monitor to a graphics card or VGA splitter or amplifier
- Additionally with two ferrite cores and DDC functionality
- 3 coax lines for the RGB signals and 9 AWG28 wires (all pins connected, incl. pin 9 and pin 15)
- Double screened cable (braided and foil shielding)
- Thumbscrews

Technical specifications

ManufacturerROLINEProduct groupCableProduct typeVGA CablesColourblackLength15 mside 1 connectorD-Sub HD15 MSide 2 connectorHD D-Sub 15-pin (HD-15), VGASide 1 ConnectorMale	-	
Product typeVGA CablesColourblackLength15 mside 1 connectorD-Sub HD15 MSide 2 connectorD-Sub HD15 MSide 1 Connector TypeHD D-Sub 15-pin (HD-15), VGASide 1 ConnectorMale	Manufacturer	ROLINE
ColourblackLength15 mside 1 connectorD-Sub HD15 Mside 2 connectorD-Sub HD15 MSide 1 Connector TypeHD D-Sub 15-pin (HD-15), VGASide 1 ConnectorMale	Product group	Cable
Length15 mside 1 connectorD-Sub HD15 Mside 2 connectorD-Sub HD15 MSide 1 Connector TypeHD D-Sub 15-pin (HD-15), VGASide 1 ConnectorMale	Product type	VGA Cables
side 1 connectorD-Sub HD15 Mside 2 connectorD-Sub HD15 MSide 1 Connector TypeHD D-Sub 15-pin (HD-15), VGASide 1 ConnectorMale	Colour	black
side 2 connector D-Sub HD15 M Side 1 Connector Type HD D-Sub 15-pin (HD-15), VGA Side 1 Connector Male	Length	15 m
Side 1 Connector TypeHD D-Sub 15-pin (HD-15), VGASide 1 ConnectorMale	side 1 connector	D-Sub HD15 M
Side 1 Connector Male	side 2 connector	D-Sub HD15 M
	Side 1 Connector Type	HD D-Sub 15-pin (HD-15), VGA
		Male

Side 2 Connector Type	HD D-Sub 15-pin (HD-15), VGA
Side 2 Connector Gender	Male
Area of application	External
Cable shielding	Double screened
Hand locking screws	Yes
Technical particularity	With two ferrite cores and DDC functionality