



OPERATING & ASSEMBLY INSTRUCTION

NAC3FPX-TOP & NAC3FPX-WOT-TOP

powerCON® TRUE1 TOP | APPLIANCE OUTLET

OPERATING INSTRUCTION


Application:

The powerCON TRUE1 system is certified as a connector with breaking capacity according IEC 60320, VDE 0625. It is intended for use as an appliance coupler and interconnection coupler. It serves to supply power to an appliance and from an appliance to other equipment. To be installed by qualified person only.

CONNECTOR ASSIGNMENT:


APPLIANCE INLET

NAC3MPX-TOP
NAC3MPX-WOT-TOP
Power IN




NAC3FX-W-TOP
(Connector)

APPLIANCE OUTLET



NAC3MX-W-TOP
(Plug connector)




NAC3FPX-TOP
NAC3FPX-WOT-TOP
NAC3FPX-ST-TOP
Power OUT


NAC3FX-W-TOP
(Connector)

APPLIANCE INLET / OUTLET ► Combination

NAC3PX-TOP
Power IN



Power OUT



NAC3MX-W-TOP
(Plug connector)


powerCON TRUE1 TOP line is full backward compatible with the preceding powerCON TRUE1 products.

UL50E environmental rating


Enclosure Type 4 when installed with sealing cover SCNAC-FPX and cover closed or when mated with attachment plug NAC3MX-W-TOP.

ASSEMBLY INSTRUCTION

NAC3FPX-WOT-TOP




NAC3FPX-TOP




Flat tabs for FASTON®
6.35 mm x 0.8 mm
(1/4" x 0.03")

WIRING



Attention:
Tightening torque
 $M_A = 40 \text{ Ncm}$.

Panel Cutout (Rear Side)



Find more details of powerCON TRUE1 TOP on www.neutrik.com.

Neutrik AG
Neutrik USA Inc.
Neutrik (UK) Ltd.
Neutrik Vertriebs GmbH
LI
USA
UK
DE/NL/AT/DK
T: +423 / 237 24 24
T: +1 704 / 972 3050
T: +44 1983 / 811 441
T: +49 8131 / 280 890
F: +423 / 232 53 93
F: +1 704 / 438 9202
F: +44 1983 / 811 439
F: +49 8131 / 280 830

Neutrik France
Neutrik Tokyo Ltd.
Neutrik Hong Kong Ltd.
Neutrik India Pvt. Ltd.
FR
JP
HK
IND
T: +33 1 / 4131 6750
T: +81 3 / 3663 4733
T: +852 / 2687 6055
T: +91 / 982 05 43 424
F: +33 1 / 4131 0511
F: +81 3 / 3663 4796
F: +852 / 2687 6052
F: +91 / 22 26163 540

Draft. Nr.: BDA 545 | Update: 11.07.2018 | Data subject to change without prior notice. © 2018 NEUTRIK®, NEUTRIK® are registered trademark of NEUTRI AG. ALL RIGHTS RESERVED.

www.neutrik.com

NEUTRIK