

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0190340002](#)  
**Status:** **Active**  
**Overview:** [Snap Plugs and Receptacles](#)  
**Description:** InsulKrimp Snap Plug, for 18-22 AWG Wire, 24.13mm Length

**Documents:**

[3D Model](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E152602

**General**

Product Family Quick Disconnects  
 Series [19034](#)  
 Crimp Quality Equipment Yes  
 Insulated Partial  
 Overview [Snap Plugs and Receptacles](#)  
 Product Name InsulKrimp  
 Type Snap Plug  
 UPC 800753047273

**Physical**

Barrel Type Closed  
 Flammability 94V-0  
 Gender Male  
 Glow-Wire Capable No  
 Insulation PVC  
 Lock to Mating Part None  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 1.426/g  
 Orientation Straight  
 Packaging Type Bag  
 Tab Thickness N/A  
 Tab Width N/A  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 3.60mm max.  
 Wire Size AWG 18, 20, 22

**Electrical**


Voltage - Maximum 600V

**Material Info**

Engineering Number A-259X

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
 Sales Drawing SD-19034-004



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/88/2018 (15  
 January 2019)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19034 Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
PremiumGrade Hand Crimp Tool	<a href="#">640010100</a>
Hand Crimp Tool	<a href="#">640010300</a>
Crimp Head for the AT-200 Pneumatic Hand Tool	<a href="#">640050100</a>
Crimp Head for the AT-200 Pneumatic Hand Tool	<a href="#">640050300</a>