

BULKHEAD INTERFACE PORT

Through Panel Power and Programming Ports



BIP SERIES - BULKHEAD INTERFACE PORT

For Convenient Power Supply and Programming

Safely access high voltage panels with the Bulkhead Interface Ports. The BIP Series provide a secure gateway to your control cabinet, enabling you to plug-in to power and program without putting you or your operation at risk.

Ten different models feature a variety of connection options such as D-Sub, USB, RJ45, duplex, simplex, and GFI's to support all your power and communication needs. Push-in CAGE CLAMP® connections provide simple, reliable and tool-free wiring on the duplex models for power connections. A metal on metal spring roller latch ensures a water tight seal.

All bulkhead interface ports are encased in an all metal housing designed to withstand tough conditions and meet the safety requirements of cULus.



Description	ltem No.	Image	Dimensional Drawing	Dimensions
Duplex outlet with one RJ45 and one USB interface connection with 3 A circuit breaker	8000-0100/ 1000-0357		50 (126)	5.0 x 3.6 in
Duplex GFI outlet with one RJ45 interface connection	8000-0100/ 1000-0362		50 (126)	5.0 x 3.6 in
Duplex outlet with one RJ45 interface connection with 3 A circuit breaker	8000-0100/ 1000-0359		50 (126)	5.0 x 3.6 in
Duplex GFI outlet with one RJ45 interface connection with 3 A circuit breaker	8000-0100/ 1000-0361	-	5.0 (126)	5.0 x 3.6 in
Simplex outlet with one RJ45 interface connection	8000-0100/ 1000-0354		45 (116)	4.5 x 1.8 in
Simplex outlet with 9 pin D-Sub interface connection	8000-0100/ 1000-0363		45 (116)	4.5 x 1.8 in
Simplex outlet with one RJ45 and two USB interface connections	8000-0100/ 1000-0355		45 (116) 18 45)	4.5 x 1.8 in
Simplex outlet with one RJ45 and one USB interface connection	8000-0100/ 1000-0356		7 [17]	4.5 x 1.8 in
One RJ45 interface connection	8000-0100/ 1000-0358		32 (83)	3.2 x 1.8 in
One 9 pin D-Sub interface connection	8000-0100/ 1000-0360		32 (83)	3.2 x 1.8 in

WAGO Corporation N120 W19129 Freistadt Road Germantown, Wisconsin 53022 Telephone: 800 / DIN-Rail (346-7245) Fax: 262 / 255-3232 info.us@wago.com www.wago.us

WAGO Canada Inc.
4145 North Service Rd., Unit 224
Burlington, ON
L7L 6A3
Telephone: 888 / WAGO 221 (924-6221)
info.ca@wago.com
www.wago.ca

WAGO SA DE CV Carretera estatal 431 Km. 2+200. Lote 99 6 Parque Industrial Tecnologico Innovacion Queretaro El Marques, Qro. 76246 Lada sin Costo: 01 800 288 WAGO (288-9246) Telefono: 422 / 221-5946 info.mx@wago.com www.wago.mx

WAGO is a registered trademark of WAGO Verwaltungsgesellschaft mbH.

"Copyright – WAGO Kontakttechnik GmbH & Co. KG – all rights reserved. The content and structure of the WAGO Websites, catalogs, videos, and other WAGO media are subject to copyright. The dissemination or changing of the content of these pages and videos is not permitted. Furthermore, the content may neither be copied nor made available to third parties for commercial purposes. Also subject to copyright are the images and videos that were made available to WAGO Kontakttechnik GmbH & Co. KG by third parties."