

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0334826201](#)  
**Status:** **Active**  
**Overview:** [MX150 Sealed and Unsealed Connector System](#)  
**Description:** MX150 Sealed Male Connector, Dual Row, 12 Circuits, Polarization A, without Connector Position Assurance, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-33472-100-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-31300-635-001 (PDF)</a>
<a href="#">Product Specification PS-33472-000-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Housings
Series	<a href="#">33482</a>
Application	Power, Wire-to-Wire
More Detailed Tech Information	<a href="http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership">http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership</a>
Overview	<a href="#">MX150 Sealed and Unsealed Connector System</a>
Product Name	MX150
UPC	889056544351


**Physical**

Circuits (maximum)	12
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	14.937/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-33472-100-001
Packaging Specification	PK-31300-635-001
Product Specification	PS-33472-000-001
Sales Drawing	SD-33482-0001-001, SD-33482-0002-001



Series image - Reference only

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[33482](#) Series

**Mates With**

[33472](#) Female Dual Row Sealed Connector

**Use With**

[33000](#) MX150 Tin (Sn) Male Terminal,  
[33011](#) Gold (Au) Male Terminal, [343450001](#)  
MX150 Cavity Plug Sealed, MX150  
Backshell [349501210](#) , [349501220](#)