


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1461860200](#)
Status: **Active**
Overview: Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee
Description: GPS and Wi-Fi 2.4GHz / 5GHz Combo Flex Antenna, 18.00mm Width, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors

Documents:

3D Model	Packaging Specification 1461860100-000 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-146186-100-001 (PDF)	Product Literature (PDF)
Application Specification AS-146186-100-001 (PDF)	



General

Product Family	Antennas
Series	146186
Component Type	Flexible Antenna with Cable
Function	Signal
Mates With	734120110 Microcoaxial RF, 50 Ohm
Overview	Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee
Product Literature Order No	987651-3851
Product Name	2.4/5GHz GPS-Wi-Fi Antenna
Protocol	BeiDou, BLE, BT, Galileo, GLONASS, GPS, Thread, Wi-Fi, Wireless Hart, Zigbee
Type	Combo Wi-Fi/GNSS Antenna
UPC	889056433631

Physical

Cable Length	200.00mm
Length	53.00mm
Mounting Style	Adhesive
Net Weight	1.182/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	18.00mm

Electrical

Band#1 F_End (MHz)	1602
Band#1 F_Start (MHz)	1575.42
Band#2 F_End (MHz)	2483.5
Band#2 F_Start (MHz)	2400
Band#3 F_End (MHz)	5850
Band#3 F_Start (MHz)	5150
Band#4 F_End (MHz)	6000
Band#4 F_Start (MHz)	3000
Electrical Connectivity	Cable
Peak Gain (dBi)	2.7 @ 1575 MHz, 2.7 @ 2.4 GHz, 3.5 @ 5 GHz, 4.2 @ 3 GHz
Return Loss - S11 (dB)	< -10
Total Efficiency	>62% @ 5 GHz, >65% @ 1575 MHz, >70% @ 2.4 GHz, >71% @ 3 GHz

Material Info

Reference - Drawing Numbers

Application Specification	AS-146186-100-001
---------------------------	-------------------

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[146186 Series](#)

Packaging Specification
Product Specification
Sales Drawing

1461860100-000
PS-146186-100-001
SD-146186-050-001

This document was generated on 03/27/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION