

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008500135](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK 254 Crimp Terminal 4809, 22-30 AWG, Hot Tin Dip, Reel](#)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification 48090001-PK-000 \(PDF\)](#)
[Product Specification PS-10-07-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-99020-0088-001 \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
Series [4809](#)
Application [Signal, Wire-to-Board](#)
Crimp Quality Equipment [Yes](#)
Overview [KK® Interconnect System - Molex](#)
Packaging Alternative [08500136 \(Loose\)](#)
Product Name [KK 254](#)
UPC [883906517830](#)

Physical

Gender [Female](#)
Material - Metal [Brass](#)
Material - Plating Mating [Tin](#)
Material - Plating Termination [Tin](#)
Net Weight [1.780/g](#)
Packaging Type [Reel](#)
Plating min - Mating [1.016µm](#)
Plating min - Termination [1.016µm](#)
Termination Interface: Style [Crimp or Compression](#)
Wire Insulation Diameter [1.57mm max.](#)
Wire Size AWG [22, 24, 26, 28, 30](#)
Wire Size mm² [N/A](#)

Material Info

Engineering Number [4809-\(P918\)](#)

Reference - Drawing Numbers

[Packaging Specification 48090001-PK-000](#)
[Product Specification PS-10-07-001, PS-99020-0088-001](#)
[Sales Drawing SD-4809-X](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[4809 Series](#)

Use With

[6471](#) 2.54mm Pitch KK Crimp Terminal Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	11030022
Terminator Die	11402102
Insertion Tool	638120000
Mini-Mac for Cat Ear and Anti-Fish Hook Crimp Terminals, 22-30 AWG Wire	638887100

This document was generated on 04/16/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION