

Tool set electrician



assorted 31-pcs. in bag

9300-035

Order-No.  1
41241

Fastening / jamming

⊖ Screwdriver SoftFinish® electric slimFix Slotted, Tool tested at 10,000 V AC / 3,5 x 100 (35446) / 5,5 x 125 (35391)

⊕ Screwdriver SoftFinish® electric slimFix Phillips, Tool tested at 10,000 V AC / PH1 x 80 (35393) / PH2 x 100 (35394)

⊖ ⊕ ⊕ ⊕ Screwdriver with bit magazine magnetic (32901)
1 x 6,5 / 1 x PH1 / 1 x PH2 / 1 x PH3 / 1 x PZ2 / 1 x T15 / 1 x T20 / 1 x T25

⊕ ⊕ ⊕ 1 x PH2 / 1 x PZ1 / 1 x PZ2 / 1 x PZ3 / 1 x T10 / 1 x T15 / 1 x T20 / 1 x T25 / 1 x T30 / 1 x T40 / 1 x Bit holder magnetic, 58 mm 1/4"

Trimming / cutting

⚡ Diagonal cutters Professional electric with DynamicJoint®, Tool tested at 10,000 V AC / 160mm, 6 1/2" (26741)

Supplying / holding

Combination pliers Professional electric with DynamicJoint® and OptiGrip with extra long cutting edge, Tool tested at 10,000 V AC / 180mm, 7" (26708)

Stripping/ insulating / crimping

Stripping tool automatic up to 6 mm² in blister pack 190mm, 7 1/2" (36050)

Surveying/marketing/measuring/checking

⊖ Voltage tester SoftFinish® single-pole, 110-250 volts (34745)
Folding ruler Longlife 2 m metric, 10 segments (27057)

Tool set electrician



assorted 12-pcs. in bag

9300-025

Order-No.  1
36389

Fastening / jamming

⊖ Screwdriver SoftFinish® electric slimFix Slotted, Tool tested at 10,000 V AC / 3,5 x 100 (35446) / 4,5 x 125 (35501) / 5,5 x 125 (35391)

⊕ Screwdriver SoftFinish® electric slimFix Pozidriv, Tool tested at 10,000 V AC / PZ1 x 80 (35395) / PZ2 x 100 (35396)

Trimming / cutting

⚡ Cable cutter Professional electric, Tool tested at 10,000 V AC / 200mm, 8" (34744)

Supplying / holding

⊖ Needle nose pliers Professional electric with cutting edge straight shape, Tool tested at 10,000 V AC / 200mm, 8" (26727)

⚡ Heavy-duty diagonal cutters Professional electric with DynamicJoint® with switchable opening spring 180mm, 7" (41274)

Stripping/ insulating / crimping

Stripping tool automatic up to 6 mm² in blister pack 190mm, 7 1/2" (36050)

Stripping tool with self-rotating trailing blade 165mm, 6 1/2" (35969)

Surveying/marketing/measuring/checking

⊖ Voltage tester SoftFinish® single-pole, 110-250 volts (34745)
Folding ruler Longlife 2 m metric, 10 segments (27057)