

HARAX M8-S female 4-pole



| | |
|--------------------|---|
| Part number | 21 02 151 2405 |
| Specification | HARAX M8-S female 4-pole |
| HARTING eCatalogue | https://b2b.harting.com/21021512405 |

Identification

| | |
|----------------|------------------------|
| Category | Connector |
| Series | Circular connectors M8 |
| Identification | M8-S |
| Element | Cable connector |
| Specification | Straight |

Version

| | |
|--------------------|--|
| Termination method | HARAX [®] connection technology |
| Gender | Female |
| Locking type | Screw locking |
| Shielding | Unshielded |
| Number of contacts | 4 |
| Coding | A-coding |

Technical characteristics

| | |
|-------------------------|-------------------------------|
| Conductor cross-section | 0.14 ... 0.34 mm ² |
| Conductor cross-section | AWG 26 ... AWG 22 |
| Wire outer diameter | ≤1.6 mm |
| Rated current | 4 A |
| Rated voltage | 32 V |
| Rated impulse voltage | 1.5 kV |
| Pollution degree | 3 |
| Insulation resistance | > 10 ⁸ Ω |
| Contact resistance | ≤10 mΩ |



Pushing Performance

Technical characteristics

| | |
|--|-----------------------------------|
| Ambient temperature | -40 ... +85 °C |
| Tightening torque | 0.4 Nm |
| Wrench size | A/F 9 Knurled screw / knurled nut |
| Mating cycles | ≥100 |
| Degree of protection acc. to IEC 60529 | IP67 in locked position |
| Cable diameter | 2.5 ... 5.1 mm |
| Overvoltage category | III |
| Isolation group | I (600 ≤ CTI) |

Material properties

| | |
|-----------------------------|----------------------------|
| Material (insert) | Polyamide |
| Material (contacts) | Copper alloy |
| Surface (contacts) | Gold plated |
| Material (hood/housing) | Polyamide Zinc die-cast |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |

Specifications and approvals

| | |
|----------------|--|
| Specifications | IEC 61076-2-104 |
| UL / CSA | UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079 |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 14.9 g |
| Country of origin | Germany |
| European customs tariff number | 85366990 |
| eCl@ss | 27440102 Circular connector (for field assembly) |