

DESCO WRIST STRAP SELECTION CHART

Wrist Straps & Coil Cords

Environmental Type

Band	Field Service	Standard Industrial	Critical
Metal	X	X	X
Elastic	X	X	
Disposable	X	X (Visitors)	

Single-Wire

Desco Wristband	Band Material	Coil Cord	Closure Type	Other Feature
Jewel® Elastic MagSnaps	Silver impregnated elastic nylon	MagSnap	Patented cam-lock	Replaceable band
Jewel® Metal Expansion MagSnaps	Expandable metal band	MagSnap	One size fits all	Superior skin contact
Jewel® Elastic Adjustable Wrist Straps	Silver impregnated elastic nylon	Machined stud / socket, 4mm	Adjustable metal locking clasp	Choice of cap Jewel® colors; replaceable grey band
Premium Metal Expansion Wrist Straps	Expandable metal band	Machined stud / socket, 4mm	One size fits all	Superior skin contact
Elastic Adjustable Wrist Straps	Silver impregnated elastic nylon	Machined stud / socket, 4mm	Adjustable metal locking clasp	Replaceable blue band
Lightweight Elastic Adjustable Wrist Straps	Silver impregnated elastic nylon	Machined stud / socket, 4mm	Adjustable metal locking clasp	Lightweight band
Hook and Loop Wrist Straps	Non-reactive conductive strip	Machined stud / socket, 4mm	Hook and Loop	Choice for sensitive skin
Disposable Wrist Straps	Dissipative viny	N/A	Slipknot cinch	For one time use

Dual-Wire

Jewel® Adjustable Dual-Wire MagSnaps Wrist Strap	Silver impregnated elastic nylon	MagSnap	Cam-lock opposite buckle	Replaceable band
Jewel® Metal Dual-Wire MagSnaps	Expandable metal	MagSnap	N/A	Superior skin contact
Jewel® Premium Metal Dual-Wire Wrist Straps	Expandable metal	MagSnap	N/A	Superior skin contact
Jewel® Dual Wire Wrist Strap with Adjustable Elastic Wristband	Silver impregnated elastic nylon	Two Machined studs / socket, 4mm	Adjustable clasp opposite buckle	Onyx black clasp
Dual-Wire Adjustable Elastic Wrist Straps	Silver impregnated elastic nylon	Two Machined studs / socket, 4mm	Adjustable clasp opposite buckle	Comfortable elastic band

Single-Wire

Desco Coil Cords	Termination	Flex Test	Other Feature	Length (ft)
Jewel® MagSnap	MagSnap / straight banana	>1,000,000	Relaxed Retraction	6, 12, 20
Jewel® Rapid Retraction	4mm socket, straight banana	>50,000,000	Choice of cord Jewel® colors	6, 10
Relaxed Retraction	4mm socket, straight banana	>1,000,000	Black cord	6, 12, 20

Dual-Wire

Jewel® Dual-Wire MagSnap	MagSnap / right angle banana 3.5mm phono plug	>11,000,000	Compatible w/ 3M & other brand continuous monitors	6, 12, 18
Jewel® Dual-Wire Cord	Snap-one, 4mm 3.5mm phono plug	>11,000,000	Compatible w/ 3M & other brand continuous monitors	6, 12, 18
Dual-Wire Snap-One Coil Cord	Snap-one, 4mm 3.5mm phono plug	>20,000	Compatible w/ 3M & other brand continuous monitors	6, 12, 18
Dual-Wire Dual-Snap Coil Cord	Two 4mm or 7mm sockets 3.5mm phono plug	>20,000,000	Compatible w/ 3M & other brand continuous monitors	6, 12

