# Mini AC Leakage Current Tester





#### **Features**

- High resolution to 100µA AC
- 3-1/2" Digit 1999 count LCD Display
- White LED backlight
- Auto power off
- 1.2" Jaw opening

### **Specifications**

Display	3-1/2 (1999 count) Digit LCD with white LED backlight		
Overload Indication	"OL" displayed on the LCD		
Display Rate	2 readings/second, nominal		
Battery	Two "1.5V" batteries		
Low Battery Indication	"B" Displayed on the LCD		
Auto OFF	Approx. 15 minutes		
Operating Conditions	0°C to +30°C (32°F to 86°F) 90%RH; +30°C to +40°C (86°F to 104°F) 75%RH; +40°C to +50°C (104°F to 122°F) 45%RH		
Storage Conditions	-25°C to +60°C (-14°F to +140°F) <90% Relative Humidity		
Altitude	Operate at less than 3000 meters		
Weight	225g (including batteries)		
Dimensions (H×W×D)	182mm × 61mm × 34mm		
Jaw Opening	1.2"		
Standard	EN61010-1, EN61010-2-032, Category II 600V		
Warranty	12 Months		

## **Range Specifications**

Function	Range	Resolution	Accuracy
AC Current (60Hz)	200mA	100μΑ	±(5.0% of reading + 8 digits)
	2A	1mA	±(5.0% of reading + 10 digits)
	200A	100mA	±(2.5% of reading + 10 digits)

#### **Part Number Table**

Description	Part Number
Mini AC Leakage Current Tester, 200A	MP780050

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Page <1>

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

