

PRODUCT BROCHURE FG PRESET PRECISION TORQUE SCREWDRIVER

"HAND ME THE MOUNTZ!"

Mountz FG Precision Preset Torque Screwdriver

THE MOST ADVANCED HAND DRIVER IN THE WORLD

- Unmatched quality you can count on
- Calibration life 4x ISO standards
- Two year unlimited warranty
- Lifetime warranty against manufacturer defects
- Accuracy and precision delivered for all fastening applications



THIS IS WHAT CONFIDENCE FEELS LIKE



50 years of innovation in the palm of your hand

THE STATE-OF-THE-ART PRECISION TORQUE DRIVER.

Engineered and assembled in Silicon Valley, the Mountz FG line of precision preset torque screwdrivers are the most advanced hand tools in the world.

Preset hand torque screwdrivers are ideal for fastening applications where operators repeatedly assemble parts at the same torque setting. These cam-over drivers include a highly sophisticated locking mechanism, a sleek and ergonomic design, and a low-impact reset mechanism to deliver the highest level of performance and comfort available.

Precision and accuracy delivered every time

BREAKTHROUGH ACCURACY AND REPEATABILITY INCREASES OPERATOR CONFIDENCE AND OVERALL QUALITY OF ASSEMBLY.

Mountz FG tools stay in calibration 4X longer than the most stringent industry standard (ISO 6789). Engineered with a cam-over mechanism, the poka-yoke screwdriver prevents over torque. You can give Mountz FG tools to any operator and have the confidence that they will deliver the correct torque, time after time.

Our unique bearing system eliminates axial (end) and side loads by the operator, increasing consistency of torque delivered and joint reliability.





Torque tools that turn heads

INNOVATIVE AND ERGONOMIC, YES. SLEEK AND BEAUTIFUL, ABSOLUTELY!

Innovative, ergonomic, sleek, stunning. In this revolutionary new precision torque tool line, Mountz has integrated industry-changing design improvements that boost accuracy, increase productivity, and dramatically expand longevity. These tools define performance. And, they are sleek and great feeling tools! So you better get used to hearing workers say, "Hand me the Mountz."



The last precision torque screwdriver you'll ever need to buy!

We've tested them over millions of cycles in our controlled lab environment and we still can't break them!

It's why we have an industry-leading warranty.

- Mountz FG tools are the only cam-over drivers on the market to offer a two year unlimited warranty. If it breaks in any way, we'll fix it or replace it for free.
- Lifetime guarantee against manufacturing defects.
- Warranty includes a free calibration within the first year.

PRODUCT OVERVIEW

FEATURE	WHAT IS IT?	ADVANTAGE	END USER BENEFIT
Cycles Before Calibration	• ISO 6789-1:2017 calls for maximum of 5,000 torque applications	 Exceeds standards Mountz 4x ISO standards: 20,000 cycles before re-calibration 	 Longer time on the production line Reduces calibration budget and down time
Consistency	 Lifecycle testing of well over 3 million combined torque applications 	Confidence every tool meets requirements	 Reduces need to replace tools/parts Lower required tool inventory
Cam & Clutch Design	 Eliminate overtorque Anti-backlash, one way, CW and CCW all available 	 Eliminates fastener breakage issues Multiple cam options for numerous applications 	 Higher line productivity Error proofing assembly process
Handle Flutes	Sleek 4-flute handle design	• Ergonomic	Sleek and comfortableEasy to clean
Needle Thrust Bearing	 Rotary bearing to allow rotation between parts 	 Reduces axial load torque dependency Reduces friction influence on tool output Longer life on internal components 	Higher accuracyDurability
Metal End Cap	 Eliminates possibility of damage to end cap 	• Durable and doesn't strip out like plastic	Fewer parts need replacementEasier to service
Bit Retention (Universal Bit Holder)	 ¼ inch female hex bit holder that grips any type of bit Patented One Touch bit release 	 Safe and secure No band / spring and captive ball to fall out 	 Better quality and productivity on line Bits don't fall out or into assembly operation
Locking Mechanism	 Double locking mechanism to prevent accidental torque setting change 	 Avoids torque setting drift 	 Longer period before re-calibration Higher accuracy over time
Poka-yoke design	Cam-over actionColored label variations	 Will not over-torque Supports assembly floor QA processes 	 Error-proofing and workers safety Better quality products at the end of the line



MOUNTZ FG PRESET PRECISION HAND SCREWDRIVER LINEUP

MODEL	ITEM NO.	TORQUE RANGES			LABEL	MEIGHT	
		AMERICAN	S.I.	DRIVE SIZE	COLOR	WEIGHT	LENGTH
FG-8i	076546	0.8-8 lbf.in	9-90 cN.m	1/4" F/Hex	Blue	7.3 oz.	5.2"
FG-8i	076551	0.8-8 lbf.in	9–90 cN.m	1/4" F/Hex	Red	7.3 oz.	5.2"
FG-8i	076556	0.8-8 lbf.in	9–90 cN.m	1/4" F/Hex	Green	7.3 oz.	5.2"
FG-8i	076561	0.8-8 lbf.in	9–90 cN.m	1/4" F/Hex	Gold	7.3 oz.	5.2"
FG-20i	076547	2–20 lbf.in	22–226 cN.m	1/4" F/Hex	Blue	7.3 oz.	5.2"
FG-20i	076552	2–20 lbf.in	22–226 cN.m	1/4" F/Hex	Red	7.3 oz.	5.2"
FG-20i	076557	2-20 lbf.in	22-226 cN.m	1/4" F/Hex	Green	7.3 oz.	5.2"
FG-20i	076562	2-20 lbf.in	22-226 cN.m	1/4" F/Hex	Gold	7.3 oz.	5.2"
FG-40i*	076548	4-40 lbf.in	0.4-4.5 N.m	1/4" F/Hex	Blue	11.5 oz.	6.3"
FG-40i*	076553	4-40 lbf.in	0.4-4.5 N.m	1/4" F/Hex	Red	11.5 oz.	6.3"
FG-40i*	076558	4-40 lbf.in	0.4-4.5 N.m	1/4" F/Hex	Green	11.5 oz.	6.3"
FG-40i*	076563	4-40 lbf.in	0.4-4.5 N.m	1/4" F/Hex	Gold	11.5 oz.	6.3"
FG-125i*	076549	25–125 lbf.in	2.8–14.1 N.m	1/4" F/Hex	Blue	11.5 oz.	6.3"
FG-125i*	076554	25–125 lbf.in	2.8–14.1 N.m	1/4" F/Hex	Red	11.5 oz.	6.3"
FG-125i*	076559	25–125 lbf.in	2.8–14.1 N.m	1/4" F/Hex	Green	11.5 oz.	6.3"
FG-125i*	076564	25–125 lbf.in	2.8–14.1 N.m	1/4" F/Hex	Gold	11.5 oz.	6.3"

Designed and manufactured to meet or exceed the accuracy and repeatability requirements of ISO 6789: 2017 (+/- 6% of setting).

Color coding labels allows for torque setting identification in manufacturing area.





*A removable, sliding T-bar is supplied with FG-40i and FG-125i models.

Note: IFR (Impact Free Resetting) and OWC (One-Way Clutch with Locking Mechanism) screwdriver models are available.

Tamper-proof internal adjustment. No external adjustment scale—must be preset using a torque analyzer.

At Mountz, we take great pride in knowing that our advanced torque tools will end up in the right hands.

mountz:

III) mountz

TOUL (III)

.zinom

mountz•





mountztorque.com

ABOUT MOUNTZ

Mountz, The Torque Tool Specialists[®], has been a leader in the torque tool industry for more than 50 years. Engineered in the Silicon Valley and serving the globe, Mountz focuses on delivering high-quality torque products, services, and solutions to ensure customers can always proceed with confidence. We are committed to forging a safer world through precision and accuracy, and by innovating every day.

SILICON VALLEY HEADQUARTERS AND SERVICE CENTER

1080 N. 11th St., San Jose, CA 95112 408-292-2214 / M–F 6am–5pm PST ALABAMA DISTRIBUTION AND SERVICE CENTER 19051 Underwood Road, Foley, AL 36535

Copyright © 2019 Mountz Inc. All Rights Reserved. V2/081319