

Thermal transfer printer - THERMOMARK PRIME - 5148888

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Mobile thermal transfer printer for card materials, including power supply unit, power cable, and USB cable. Support CD includes user manuals in several languages, links to firmware; driver, and planning and marking software. User manual printed in German and English. Magazine for UCT-TM... sheets and magazines for US-... cards. One Pcs./Pkt. each UCT-TM 6, US-EMLP (85,6x54), ink ribbon cartridge = 70 m

Product Description


THERMOMARK PRIME was developed for mobile or stationary operation. It is equipped with a 7" color touch display, integrated "MARKING system app" marking software on board, and a replaceable battery pack. You can easily create high-quality printed labels and markers in UCT, US, and UM format.

Your advantages

- ✓ Easy data entry, thanks to fully integrated marking software (MARKING system app) and multi-touch display with stand. Additional control possible via PROJECT complete.
- ✓ Automatic ink ribbon, magazine and material detection prevents printing errors
- ✓ Simple material and ink ribbon replacement in less than 10 seconds
- ✓ Fast, high-quality, and durable printing; printing time for one card is less than 8 seconds.
- ✓ 100% independent, thanks to replaceable high-performance rechargeable batteries
- ✓ Maintenance-free operation with proven thermal transfer printer technology in 300 dpi print resolution
- ✓ Flexible areas of application with more than 600 different marking materials for marking a wide range of applications

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 041834
GTIN	4055626041834
Weight per Piece (excluding packing)	9,000.000 g
Custom tariff number	84433210
Country of origin	Germany

Technical data

General

Interface	10/100 Mbps Ethernet
	USB 2.0

Thermal transfer printer - THERMOMARK PRIME - 5148888

Technical data

General

Weight	6 kg
--------	------

Dimensions

Length	292 mm
Height	122 mm
Width	380 mm

Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC
Additional text	50 Hz ... 60 Hz

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 5.0	19020200
eCl@ss 5.1	19020200
eCl@ss 6.0	19140100
eCl@ss 7.0	19140104
eCl@ss 8.0	19140104
eCl@ss 9.0	19140104

ETIM

ETIM 5.0	EC001672
ETIM 6.0	EC001672
ETIM 7.0	EC001672

UNSPSC

UNSPSC 13.2	43212108
UNSPSC 18.0	43212108
UNSPSC 19.0	43212108
UNSPSC 20.0	43212108
UNSPSC 21.0	43212108

Approvals

Approvals

Thermal transfer printer - THERMOMARK PRIME - 5148888

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU *- DE.A*30.B.02513
-----	---	--------------------------

Accessories

Accessories

Ink ribbon

Ink ribbon cartridge - TMP-RIBBON 110 BK 100 - 0803374



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

Ink ribbon cartridge - TMP-RIBBON 110 BK 101 - 0803714



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)..., US-TM(F)L..., US-WMTB..., US-EML..., US-EML(S)P..., US-EMLP-HA..., US-EM(S)P..., US-EML-RS..., width: 110 mm, color: black

Ink ribbon cartridge - TMP-RIBBON 110 BU 100 - 0803378



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)..., US-TM(F)L..., US-WMTB..., US-EML..., US-EML(S)P..., US-EMLP-HA..., US-EM(S)P..., US-EML-RS..., width: 110 mm, color: blue

Thermal transfer printer - THERMOMARK PRIME - 5148888

Accessories

Ink ribbon cartridge - TMP-RIBBON 110 GN 100 - 0803380



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: green

Ink ribbon cartridge - TMP-RIBBON 110 RD 100 - 0803377



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: red

Ink ribbon cartridge - TMP-RIBBON 110 WH 100 - 0803376



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: white

Ink ribbon cartridge - TMP-RIBBON 110 YE 100 - 0803379



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: yellow

Magazine

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards

Thermal transfer printer - THERMOMARK PRIME - 5148888

Accessories

Magazine - TMP-UCT-MAG1 - 0803342



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-TM..., UCT1(U)-TM..., UCT5-TM..., UCT-EM (5x10), UCT-EM (6x10)

Magazine - TMP-UCT-MAG2 - 0803343



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-TMF...

Magazine - TMP-UCT-MAG3 - 0803344



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMS...

Magazine - TMP-UCT-MAG4 - 0803345



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT1-TMF...

Magazine - TMP-UCT-MAG5 - 0803347



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT2-TM...

Thermal transfer printer - THERMOMARK PRIME - 5148888

Accessories

Magazine - TMP-UCT-MAG6 - 0803348



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT3-TM...

Magazine - TMP-UCT-MAG7 - 0803349



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMT..., UCT-EM (7x10)

Magazine - TMP-UCT-MAG8 - 0803350



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (20x7), UCT-EM (17,5x8)

Magazine - TMP-UCT-MAG9 - 0803351



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (12x3,3), UCT-EM (12x6)

Magazine - TMP-UCT-MAG10 - 0803352



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (30x5)

Thermal transfer printer - THERMOMARK PRIME - 5148888

Accessories

Magazine - TMP-UCT-MAG11 - 0803353



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (17x10)

Magazine - TMP-UCT-MAG12 - 0803354



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (10x8), UCT-EM (12x7)

Magazine - TMP-UCT-MAG13 - 0803355



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (10x5)

Magazine - TMP-UCT-MAG14 - 0803356



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (17x8), UCT-EM (21x8)

Magazine - TMP-UCT-MAG15 - 0803357



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (20x9)

Thermal transfer printer - THERMOMARK PRIME - 5148888

Accessories

Magazine - TMP-UCT-MAG16 - 0803358



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (17x9)

Magazine - TMP-UCT-MAG17 - 0803360



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (18x8)

Magazine - TMP-UCT-MAG18 - 0803361



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (17,5x7,5)

Magazine - TMP-UCT-MAG19 - 0803363



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (15x10)

Magazine - TMP-UCT-MAG20 - 0803364



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (10x7),
UCT-WMTB (29x8)

Thermal transfer printer - THERMOMARK PRIME - 5148888

Accessories

Magazine - TMP-UCT-MAG21 - 0803365



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (20x8)

Magazine - TMP-UCT-MAG22 - 0803366



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (17,5x9)

Magazine - TMP-UCT-MAG25 - 0803369



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMCO ... (12x4)

Magazine - TMP-UCT-MAG26 - 0803370



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EMP (25x6), UCT-EMP (29x8), UCT-EMP (40x17), UCT-EMP (60x15)

Magazine - TMP-UCT-MAG27 - 0803371



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMTBA (25x6), UCT-WMTBA (29x6), UCT-WMTBA (40x17)

Thermal transfer printer - THERMOMARK PRIME - 5148888

Accessories

Magazine - TMP-UCT-MAG28 - 0803372



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMCO ... (18x4)

Magazine - TMP-UCT-MAG29 - 0803373



Magazine for the THERMOMARK PRIME printer, for accommodating UCT-WMCO ... (23xX)

Magazine - TMP-UCT-MAG31 - 1025505



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EMNP (12.5x6)

Magazine - TMP-UCT-MAG33 - 1082130



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (12x8)

Printing system accessories

Battery - TMP/ACCU - 0803668



Replacement battery for the THERMOMARK PRIME, NiMH 18 V DC, 2.1 Ah

Thermal transfer printer - THERMOMARK PRIME - 5148888

Accessories

Power supply unit - TMP/EXT.POWER-SUPPLY 100-240V - 0803672



Replacement power supply for THERMOMARK PRIME, input voltage at 100 V AC to 240 V AC / 1.5 A / 50 Hz to 60 Hz, output voltage at 24 V DC / 4.16 A

Charger - TMP/CHARGER - 0803670



Charging device for THERMOMARK PRIME rechargeable battery (TMP/ACCU), with reverse polarity protection and operating status display; operating voltage 10.8 V to 24 V

Battery compartment cover - TMP/ACCU COVER - 0803669



The battery compartment cover provides protection against dust and dirt deposits when starting up the THERMOMARK PRIME without the battery using the mains connection

Cable - TMP/CHARGER CABLE VEHICLE 12V - 0803671



Passenger vehicle cable for charging device (TMP/CHARGER); the power supply of the charging device comes directly from a 12 V passenger vehicle cigarette lighter (input voltage 11 V to 14 V); length 1.5 m

Transport bag - TMP BAG - 0803674



Transport bag, unequipped for THERMOMARK PRIME, accessories, marking material, and consumables, weight: 2.39 kg, width: 180 mm, height: 460 mm, color: black

Thermal transfer printer - THERMOMARK PRIME - 5148888

Accessories

Case - TMP CASE - 0803675



Transport case for the THERMOMARK PRIME including accessories, marking materials, and consumables. Rounded profile case with aluminum frame, unequipped

Case - MOBILE BACKPACK - 0803717



Transport rucksack for the THERMOMARK PRIME including accessories, marking material, and consumables, unequipped
