

## Tool bag, equipped - CRIMPFOX CENTRUS 6S SET - 1213999

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cutting, stripping, and crimping set, packaged in a tools case, comprising CUTFOX 18, WIREFOX 10, CRIMPFOX CENTRUS 6S, AI SORTI BOX RD, TOOL-KIT STANDARD EMPTY

### Your advantages

- ✔ Universal tools sets with WIREFOX 10, CRIMPFOX-CENTRUS tools from TOOL fox
- ✔ Ideal for TWIN ferrule
- ✔ Rugged and heavy-duty tool bags

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 212715
GTIN	4055626212715
Weight per Piece (excluding packing)	1,355.000 g
Custom tariff number	82060000
Country of origin	Sweden

### Technical data

#### General

Color	black
-------	-------

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Articles in set

#### Crimping pliers - CRIMPFOX CENTRUS 6S - 1213144



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm<sup>2</sup> ... 6 mm<sup>2</sup>, also for TWIN ferrules up to 2 x 4 mm<sup>2</sup>, automatic cross section adjustment, lateral insertion, equipped with fall protection

## Tool bag, equipped - CRIMPFOX CENTRUS 6S SET - 1213999

### Articles in set

Range box - AI SORTI BOX RD - 3202960



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

Stripping tool - WIREFOX 10 - 1212150



Stripping tool, for cables and conductors from 0.02 - 10 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade

Tool bag, unequipped - TOOL-KIT STANDARD EMPTY - 1212423



Tool box, unequipped

Cable-cutting tool - CUTFOX 18 - 1212129



Cable cutter, angled, for copper and aluminum up to 18 mm diameter (up to 50 mm<sup>2</sup>)

## Classifications

eCl@ss

eCl@ss 10.0.1	21045003
eCl@ss 4.0	21040400
eCl@ss 4.1	21040400
eCl@ss 5.0	21040400
eCl@ss 5.1	21040400
eCl@ss 6.0	21040400
eCl@ss 7.0	21045003
eCl@ss 8.0	21045003
eCl@ss 9.0	21045003

# Tool bag, equipped - CRIMPFOX CENTRUS 6S SET - 1213999

## Classifications

### ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000149
ETIM 6.0	EC000149
ETIM 7.0	EC000149

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27113201
UNSPSC 18.0	27113201
UNSPSC 19.0	27113201
UNSPSC 20.0	27113201
UNSPSC 21.0	27113201

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------