

Stripping tool - WIREFOX 10 CUS - 1212760

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Stripping tool, laser marked according to customer specifications, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

The figure shows WIREFOX 4 CUS

Product Description


Insertable stripping blades: 1212151 WIREFOX 4/SB, 1212153 WIREFOX 16/SB, and 1212314 WIREFOX 6SC/SB, direct replacement: 1212152 WIREFOX 10/SB

Your advantages

- Flexible, adjustable limit stop for the stripping length
- Practical integrated wire cutter
- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 942768
GTIN	4046356942768
Weight per Piece (excluding packing)	207.900 g
Custom tariff number	82032000
Country of origin	Sweden
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	191 mm
Width (a)	20 mm
Height (c)	90 mm
Cable diameter	0.1 mm ... 3.7 mm
Stripping length	18 mm

General

Stripping tool - WIREFOX 10 CUS - 1212760

Technical data

General

Color	black/green
Weight	136 g
Min. cross section	0.02 mm ²
Max. cross section	10 mm ²
AWG min	34
AWG max	8

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21043706
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043700
eCl@ss 7.0	21043706
eCl@ss 8.0	21043706
eCl@ss 9.0	21043706

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC000163
ETIM 5.0	EC000163
ETIM 6.0	EC002109
ETIM 7.0	EC002109

UNSPSC

UNSPSC 13.2	27111510
UNSPSC 18.0	27111510
UNSPSC 19.0	27111510
UNSPSC 20.0	27111510
UNSPSC 21.0	27111510

Approvals

Approvals

Stripping tool - WIREFOX 10 CUS - 1212760

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

Accessories

Accessories

Knife

Spare knife - WIREFOX 10/SB - 1212152



Replacement blade for WIREFOX 10, for cables and conductors of 0.02 - 10 mm²

Spare knife - WIREFOX 4/SB - 1212151



Replacement blade for WIREFOX 4, for cables and conductors (especially for rubber and silicone insulations) of 0.1 - 4 mm²

Spare knife - WIREFOX 6SC/SB - 1212314



Replacement blade for WIREFOX 6SC, for cables and conductors (especially for cables protected against short circuits and ground leakages) 1.5 - 6 mm²

Stripping tool - WIREFOX 10 CUS - 1212760

Accessories

Spare knife - WIREFOX 16/SB - 1212153



Replacement blade for WIREFOX 16, for cables and conductors of 4 - 16 mm²

Stripping tool

Replacement limit stop - WIREFOX 10/WS - 1200285

Replacement limit stop

Replacement retaining jaw - WIREFOX 10/CJ - 1200286



Replacement clamping jaws for WIREFOX 4, WIREFOX 6SC, and WIREFOX 10