

Stripping tool - WIREFOX-D 13 - 1212162

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Stripping tool, for stripping installation lines of Ø 8 - 13 mm , e.g. NYM 3 x 1.5 mm² to 5 x 2.5 mm², single line stripping 0.2 mm² - 4 mm² , with longitudinal cut blade and sliding knife

Your advantages

- Large selection of precision stripping tools
- The right tool for every application

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 454155
GTIN	4046356454155
Weight per Piece (excluding packing)	63.500 g
Custom tariff number	82055980
Country of origin	Germany

Technical data

Dimensions

Length (b)	125 mm
Width (a)	27.5 mm
Height (c)	37 mm
Cable diameter	8 mm ... 13 mm
Stripping length	100 mm

General

Color	black
Weight	46.5 g
Min. cross section	0.2 mm ²
Max. cross section	4 mm ²
AWG min	24
AWG max	12

Environmental Product Compliance

Stripping tool - WIREFOX-D 13 - 1212162

Technical data

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21043706
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043700
eCl@ss 7.0	21043706
eCl@ss 8.0	21043706
eCl@ss 9.0	21043706

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC000163
ETIM 5.0	EC000163
ETIM 6.0	EC002109
ETIM 7.0	EC002109

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	27111510
UNSPSC 18.0	27111510
UNSPSC 19.0	27111510
UNSPSC 20.0	27111510
UNSPSC 21.0	27111510

Approvals

Approvals

Approvals

EAC

Stripping tool - WIREFOX-D 13 - 1212162

Approvals

Ex Approvals

Approval details

EAC



RU x-
DE.xx08.B.02974