


Starter kit - RAD-868-IFS-STARTERKIT - 2702073

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Radioline starter kit, consists of three wireless transceivers, two I/O extension modules (RAD-DAIO6-IFS), three antennas, CD with PSI-CONF configuration software, quick start guide, USB cable for diagnostics and extended configuration



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 941754
GTIN	4046356941754
Weight per Piece (excluding packing)	1,946.000 g
Custom tariff number	85176200
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Articles in set

Wireless module - RAD-868-IFS - 2904909



Radioline - 868 MHz wireless transceiver with RS-232/RS-485 interface, can be extended with I/O modules, RSMA (female) antenna connection, point-to-point, star, and mesh networks up to 99 stations, range of up to 20 km (with a clear line of sight), for use in Europe

Starter kit - RAD-868-IFS-STARTERKIT - 2702073

Articles in set

Wireless module - RAD-868-IFS - 2904909



Radioline - 868 MHz wireless transceiver with RS-232/RS-485 interface, can be extended with I/O modules, RSMA (female) antenna connection, point-to-point, star, and mesh networks up to 99 stations, range of up to 20 km (with a clear line of sight), for use in Europe

Wireless module - RAD-868-IFS - 2904909



Radioline - 868 MHz wireless transceiver with RS-232/RS-485 interface, can be extended with I/O modules, RSMA (female) antenna connection, point-to-point, star, and mesh networks up to 99 stations, range of up to 20 km (with a clear line of sight), for use in Europe

I/O extension module - RAD-DAIO6-IFS - 2901533



Radioline - I/O extension module, 2 digital inputs and outputs (0 ... 250 V AC/DC) and 1 analog input (0/4 ... 20 mA) and output (0/4 ... 20 mA, 0 ... 10 V)

I/O extension module - RAD-DAIO6-IFS - 2901533



Radioline - I/O extension module, 2 digital inputs and outputs (0 ... 250 V AC/DC) and 1 analog input (0/4 ... 20 mA) and output (0/4 ... 20 mA, 0 ... 10 V)

Cable for programming - RAD-CABLE-USB - 2903447



Radioline - USB data cable for communication between the PC and Radioline devices, energy supply for diagnostics and configuration via the USB port of the PC, cable length: 2 m / 6.5 ft

Classifications

eCl@ss

eCl@ss 10.0.1	19170501
eCl@ss 5.1	27230207

Starter kit - RAD-868-IFS-STARTERKIT - 2702073

Classifications

eCl@ss

eCl@ss 6.0	27230207
eCl@ss 8.0	19170201
eCl@ss 9.0	19170201

ETIM

ETIM 5.0	EC000816
ETIM 6.0	EC000816
ETIM 7.0	EC000816